Pushing Performance
Since 1945

M12 slim angled female X-cod 8-pol



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 881 4805
Specification	M12 slim angled female X-cod 8-pol
HARTING eCatalogue	https://harting.com/21038814805

Identification

Category	Connectors
Series	Circular connectors M12
Identification	Slim Design
Element	Cable connector
Specification	Angled

Version

Termination method	Crimp termination
Gender	Female
Shielding	Shielded
Number of contacts	8
Coding	X-coding
Locking type	Screw locking
Details	Please order crimp contacts separately.
Details	For Ethernet applications up to 10 Gbit only

Technical characteristics

Conductor cross-section (mm²)	0.08 ... 0.25 mm²
Conductor cross-section (AWG)	AWG 28 ... AWG 23
Wire outer diameter	≤1.4 mm
Rated current	0.5 A
Rated voltage	48 V
Rated impulse voltage	0.8 kV

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Technical characteristics

Pollution degree	3
Transmission characteristics	Cat. 6_A Class E_A up to 500 MHz
Overvoltage category	III
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s
Insulation resistance	$>10^8$ Ω
Contact resistance	≤10 mΩ
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	15
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	5.7 ... 8.8 mm
Isolation group	I (600 ≤ CTI)

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-2-109

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Specifications and approvals

UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	68.5 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140226708
eCl@ss	27440116 Circular connector (for field assembly)
ETIM	EC002635
UNSPSC 24.0	39121413

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.