

Honeywell Sensing and Control

Search



4TP14-3

(Home : Products : Switches » MICRO SWITCH™ Rocker Switches » Power-duty Rocker Switches » TP)

[contacts](#)


narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6158)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9303)
- Magnetic (538)
- Platinum thin film (56)
- Thick Film (1372)
- More...



TP Series Rocker Switch, 4 pole, 2 position, Screw terminal, Flush Panel Mounting

Actual product appearance may vary.

[Sales & Service](#)[Distributor Inventory](#)

Customer Service
Technical Support
Global Sales & Service
View Site Demo
Site Comments?

[meet dr. larry](#)

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

[my links](#)

[Login to iCOM](#)
[Login to Rep/AD Portal](#)
[Login to Digital University](#)

[News Center](#)

HONEYWELL INTRODUCES TRUSTABILITY® NSC SERIES, UNCOMPENSATED / UNAMPLIFIED BOARD MOUNT PRESSURE SENSORS

HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

[MICRO SWITCH Anniversary site](#)

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

Wireless Switches Offer Unlimited Benefit
Basic Switches Are Not Created Equal
Applying Precision Switches
Sensors for Medical Devices
New Ways to Measure Torque
Choosing Safety Switches
Specifying Hour Meters

Need help?

[Click here to contact us](#)[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Product Type	MICRO SWITCH™ Rocker										
Contact Type	Silver Cadmium Oxide Contacts										
Circuitry	4PDT										
Action	2 position										
Circuitry/Operating action	<table><thead><tr><th>Keyway Position</th><th>Opposite Keyway Position</th></tr></thead><tbody><tr><td></td><td></td></tr><tr><td></td><td></td></tr><tr><td></td><td></td></tr><tr><td></td><td></td></tr></tbody></table>	Keyway Position	Opposite Keyway Position								
Keyway Position	Opposite Keyway Position										
Mounting	Flush Panel										
Lamp Type	Translucent										
Termination	Screw										
Ampere/Voltage Range (Resistive Load)	0.5 A at 250 Vdc, 0.75 A at 115 Vdc, 0.5 A to 20 A at 0.5 Vdc to 28 Vdc, 0.5 A to 15 A at 0.5 Vac to 277 Vac										
Comment	Silver cadmium oxide contacts										
Availability	Global										
UNSPSC Code	302119										
UNSPSC Commodity	302119 Switches and controls and relays										
Series Name	TP										