





APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



Rev	AWO #	Description	Date	Appr
-		RELEASED	6/17/11	
A		REVISED SHAPE	7/24/13	
B		REVISED DIM.	2/17/14	AY/MY

SPECIFICATIONS:
Material:
Insulator: PA66, glass reinforced, rated UL 94V-2
Insulator color: White
contact: Brass, Tin plated
Electrical:
Current rating: 7 Amps max
Contact resistance: 20mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -40°C to +85°C
Environmental:



Positions: 2 thru 20
A = .156 [3.96] x No. of Positions
B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES	HOLES	DATE	TITLE
.X ± .10	ØX ± .10	6/17/11	.156 [3.96] HEADER, REVERSE RIGHT ANGLE
.XX ± .020	ØXX ± .015		
.XXX ± .015	ØXXX ± .010		
APPROVALS	DATE		
DRAWN	DY		
CHECKED			
APPROVED			

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

SIZE	PART NO.	REV.
X	LHD-XX-TRB	B
REF: S00019C	SCALE: NTS	SHEET 1 OF 1