



Color: ■ gray

Mounting accessories WINSTA® MINI 3-pole

Put your trust in tried-and-tested accuracy for the installation for the implementation of your project: The mounting accessories from the WINSTA® MINI product line. With WAGO, you benefit from a large selection of expansions for the WINSTA® product line. WINSTA® MINI is our response to the trend toward miniaturisation. Our smallest pluggable connection system is very good for lights, for example, since due to LED technology, these offer significantly less space for the connection technology.

Lower costs through fast commissioning and elimination of service expenses – solutions from WINSTA® MINI

WINSTA® is the pluggable connection system that is ideally tailored to the strict requirements of electrical installation. It ensures error-free installation of cables and components, quickly and reliably. Take advantage of the pluggable version of our maintenance-free spring pressure connection technology too! Plan your installation with with protection against mismatching from WAGO.

- compact design for conductors with a cross-section up to 1.5 mm²
- fast, secure installation

| Notes                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
|----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| General safety information | <div><b>NOTICE: Observe installation and safety instructions!</b><br/><br/><div><div>1. Only to be used by a qualified electrician or by a person electrically instructed for the task (EIP per DIN VDE 0105-100).</div><div>2. Do not install while energized or under load.</div><div>3. Use only for its intended purpose.</div><div>4. Observe applicable national regulations, standards and directives.</div><div>5. Observe the technical specifications of the products.</div><div>6. Ensure correct polarity assignment.</div><div>7. Do not use damaged or contaminated components.</div><div>8. Observe conductor types, conductor cross-sections, strip lengths and cable diameters.</div><div>9. Insert conductors up to the stop.</div><div>10. Use only with locking lever and strain relief.</div><div>11. Use original accessories only.</div></div><div><b>To be sold only with installation instructions!</b></div></div> |



Connection Data

| Connection 1 |   |
|--------------|---|
| Pole number  | 3 |

Physical data

|        |                        |
|--------|------------------------|
| Width  | 16.9 mm / 0.665 inches |
| Height | 18.9 mm / 0.744 inches |
| Depth  | 10.5 mm / 0.413 inches |

Mechanical data

|          |                     |
|----------|---------------------|
| Suitable | for socket and plug |
|----------|---------------------|

Material data

|                                    |                                                                          |
|------------------------------------|--------------------------------------------------------------------------|
| Note (material data)               | <a href="#">Information on material specifications can be found here</a> |
| Color                              | gray                                                                     |
| Insulation material (main housing) | Polyamide (PA66)                                                         |
| Flammability class per UL94        | V0                                                                       |
| Fire load                          | 0.015 MJ                                                                 |
| Weight                             | 0.6 g                                                                    |

Environmental requirements

|                                          |                                            |
|------------------------------------------|--------------------------------------------|
| Processing temperature                   | -5 ... +40 °C                              |
| Continuous operating temperature         | -35 ... +85 °C                             |
| Note on continuous operating temperature | Insulating parts for temperatures ≤ 105 °C |

Commercial data

|                       |               |
|-----------------------|---------------|
| Product Group         | 20 (Winsta)   |
| PU (SPU)              | 100 (50) pcs  |
| Packaging type        | Box           |
| Country of origin     | DE            |
| GTIN                  | 4055143838610 |
| Customs tariff number | 39269097900   |

Product Classification

|             |                      |
|-------------|----------------------|
| UNSPSC      | 39121421             |
| eCl@ss 10.0 | 27-44-06-92          |
| eCl@ss 9.0  | 27-44-06-92          |
| ETIM 9.0    | EC002863             |
| ETIM 10.0   | EC002863             |
| ECCN        | NO US CLASSIFICATION |



| Environmental Product Compliance |                        |
|----------------------------------|------------------------|
| RoHS Compliance Status           | Compliant,No Exemption |

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 890-303

↓

| Documentation |            |     |          |   |
|---------------|------------|-----|----------|---|
| Bid Text      |            |     |          |   |
| 890-303       | 19.02.2019 | xml | 2.66 KB  | ↓ |
| 890-303       | 16.03.2015 | doc | 23.50 KB | ↓ |

CAD/CAE-Data

CAD data

2D/3D Models 890-303

↓