



BMMN000505182R2MX1

Search by :

Part Number

Characteristics

Cross reference




MP

?

Closed Magnetic Circuit Type
Molding Processing & for Ultra High Current

Series Pdf

Product detail		
L(mm) ±	5.18±0.22	
W(mm) ±	5.49±0.25	
T(mm) ±	1.8Max.	
Inductance(uH)	2.2	
Tolerance(±%)	20	
Test Frequency	100kHz,0.25V	
RDC(Ω)Max	0.035	
RDC(Ω)Typ	0.03	
Isat(A)Typ	7	
Isat(A)Max	6	
Irms(A)Typ	5.2	
Irms(A)Max	4.7	
Operating Temperature	-55℃~125℃(Including self - temperature rise)	



Products

Power Inductor
EMI-Common Mode Choke
EMI-Bead
RF-Signal Inductor
RF-Passives/Antennas
LAN Transformer
Resistor & Current Sensor

Applications

Automotive
Industrial
Server/DataCenter
Communication
Mobile and Tablet
Computer/Laptop
Consumer

Design Tools

Simulation Tool
Product Search Engine
E-Catalogue

About Us

Corporate Overview
Corporate Milestones
Core Technology
Certificates & Awards
Quality and Social Responsibility

Investor

Financial Information
Corporate governance
Downloaded from Arrow.com

News

[Media Center](#)

[New Products](#)

[Events](#)

[Product Notices](#)

Contact Us

[Contact Info](#)

[Contact Form](#)

[Join Chilisin](#)

[Terms of Use](#)

[Privacy policy](#)

[Sitemap](#)



Inductor



Resistor



Powder

Copyrights © 2018. Chilisin. All rights reserved.