





- NOTES:
- MATERIAL AND FINISH (PLATING THICKNESS IN MICRO-INCHES):
BODY - BRASS, GOLD PLATING
CONTACT - BERYLLIUM COPPER, GOLD PLATING
INSULATOR - PTFE, NATURAL
 - ELECTRICAL:
 - IMPEDANCE:50 OHM
 - FREQUENCY RANGE: 0-2 GHz
 - VSWR (RETURN LOSS): 1.2 MAX.
 - DIELECTRIC WITHSTANDING VOLTAGE:1000 VRMS. (FOR ONE MINUTE)
 - CONTACT RESISTANCE: 5 mOHM MAX. (CENTER CONTACT)
1 mOHM MAX. (OUTER CONTACT)
 - VOLTAGE RATING: 500 VOLTS
 - INSULATION RESISTANCE: 10000 MOHM (AT 500V FOR ONE MINUTE)
 - MECHANICAL:
 - DURABILITY:500 CYCLES MIN.
 - TEMPERATURE RANGE:-40°C TO +85°C



SCALE 6.000



SCALE 5.000

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ±0.3mm ANGLES ±1°	MATERIAL	DRAWN JEKY.C	DATE 28-Apr-15	TITLE MCX RECEPTACLE SURFACE MOUNT			Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com		
		ENGINEER P. BRENZEL	DATE 18-Jun-98						
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE EAR 102-966929 1 MOTOROLA 0909901V01 615X-1429-100 GEN# ASSYF3_MCX	APPROVED H.HE	DATE 28-Apr-15	SCALE: 12.0:1.0 SHEET 2 OF 2			DRAWING NO. 919-118J-5IPT		
	FINISH	CAD FILE I:\MCX\919-118J-5IPT		DWG SIZE B	CODE ID 74868	REV J	ITEM NO. 919-118J-5IPT		
							PART NO. 919-118J-5IPT		