

HONEYWELL PART NUMBER
22SM401
PRODUCT CODE TXT0100

REV	DOCUMENT	CHANGED BY	CHECK
5	0038112	KVS 04JUN08	ASD

B


A

A

B

A

A



NOTE -

- △-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
- 2-TERMINALS ARE PLATED FOR SOLDERING
- 3-DEADBREAK CONDITIONS
 - (A) MAX AMOUNT PERMISSIBLE ----.0002 IN
 - (B) LOAD -----10 VAC , .035 AMP
 - (C) PLUNGER RATE -----.015 INCHES PER MIN

RELEASE NO. SR - 9701

REPLACES

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± - ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± - ANGLES ± - THIRD ANGLE PROJECTION 				DRAWN		VK		19 OCT 07		Honeywell											
OPERATING FORCE — — 3 1/2 OZ MAX		CONTACT ARRANGEMENT SPDT								CHECK		RJ		19 OCT 07								TITLE SWITCH - BASIC					
RELEASE FORCE— — — — 1 OZ MIN		30 VOLTS DC RATING								THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.						SIZE B											
DIFFERENTIAL TRAVEL— — — .001 MAX				SEA LEVEL																		50,000 FT		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			
OVERTRAVEL — — — — — .005 MIN		INDUCTIVE		3 AMP		2.5 AMP		MAXIMUM INRUSH 24 AMP						REVISIONS													
		RESISTIVE		5 AMP		5 AMP														APPROVALS						KEMA, CE 5A, 250V ~ T85 1E4  UL, CSA 5A, 250 VAC   BRAND L4	