




**Part Number :** [877592650](#)  
**Product Description :** Milli-Grid Header, Surface Mount, Vertical, 26 Circuits, 0.38µm Gold (Au) Selective Plating, with Press-fit Plastic Pegs, Lead-Free  
**Series Number :** 87759  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles



Documents & Resources


**Drawings**  
[877592650\\_sd.pdf](#)  
[PK-89990-475-001.pdf](#)

**3D Models and Design Files**  
[877592650\\_stp.zip](#)

**Specifications**  
[503940001-AS-000.pdf](#)  
[PS-87761-100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	PCB Headers and Receptacles
Series	87759
Description	Milli-Grid Header, Surface Mount, Vertical, 26 Circuits, 0.38µm Gold (Au) Selective Plating, with Press-fit Plastic Pegs, Lead-Free
Application	Board-to-Board, Signal
Component Type	PCB Header
Product Name	Milli-Grid
UPC	822348283613

#### Agency

UL	E29179
----	--------

#### Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V

#### Physical

Breakaway	Yes
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0

Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	3.80mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.651/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	None
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.381µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Surface Mount

## Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	3
Max-Temp	260

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
-------------	-------------

Milli-Grid Dual Row Receptacle Housings	<u>51110</u>
Milli-Grid Vertical Through Hole PCB Receptacles	<u>78787</u>
Milli-Grid Top Entry Surface Mount PCB Receptacles	<u>78788</u>
Milli-Grid Vertical Through Hole PCB Receptacles	<u>79107</u>
Milli-Grid Vertical Through Hole PCB Receptacles	<u>79108</u>
Milli-Grid Top/Bottom Entry Surface Mount PCB Receptacles	<u>79109</u>
Milli-Grid Top Entry Surface Mount PCB Receptacles	<u>87381</u>

---

This document was generated on Apr 25, 2025