



Part Number : [681450825](#)
Product Description : 2.50mm Pitch Wire-to-Board Header, 1.02mm Tab Type, Right Angle, 8 Circuits, Gray
Series Number : 68145
Status : Obsolete
Product Category : PCB Headers and Receptacles

Documents & Resources

Specifications

[PS-68145-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	PCB Headers and Receptacles
Series	68145
Description	2.50mm Pitch Wire-to-Board Header, 1.02mm Tab Type, Right Angle, 8 Circuits, Gray
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	N/A
UPC	756054606964

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	13V DC (RMS)

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Gray
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	3.058/g
Number of Rows	2

Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
PC Tail Length	4.00mm
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Plating min - Mating	0.813μm
Plating min - Termination	0.813μm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Closed Ends
Stackable	No
Temperature Range - Operating	-30° to +85°C
Termination Interface Style	Through Hole

This document was generated on Sep 22, 2025

Obsol