Specifications:

Contact rating:	24 V DC, 25 mA / 6 V DC, 100 mA
Contact resistance:	< 50 mΩ
Insulation resistance:	> 100 MΩ at 500 V DC
Dielectric strength:	500 V, 50 Hz for the duration of 1 minute
Operating temperature:	–40 °C to +85 °C
Mechanical life:	minimum 2 000 operations per pole
Material:	PBT meets UL 94 V–0
Contacts:	gold-plated over nickel
Construction:	case sealed
	Series DBS 2000 slide recessed, sealed with protective tape, **washable**
Mounting:	on pc-board
Slide position:	OFF
Soldering conditions:	wave-soldering – max.: 5 sec, 260 °C

Models:

Series DBS 2000

Type	Poles	Length (A)
DBS 2001	1	3.90 mm
DBS 2002	2	6.44 mm
DBS 2003	3	8.98 mm
DBS 2004	4	11.52 mm
DBS 2005	5	14.06 mm
DBS 2006	6	16.60 mm
DBS 2007	7	19.14 mm
DBS 2008	8	21.68 mm
DBS 2009	9	24.22 mm
DBS 2010	10	26.76 mm
DBS 2012	12	31.84 mm





Series DBS 2100

Type	Poles	Length (A)
DBS 2101	1	3.90 mm
DBS 2102	2	6.44 mm
DBS 2103	3	8.98 mm
DBS 2104	4	11.52 mm
DBS 2105	5	14.06 mm
DBS 2106	6	16.60 mm
DBS 2107	7	19.14 mm
DBS 2108	8	21.68 mm
DBS 2109	9	24.22 mm
DBS 2110	10	26.76 mm
DBS 2112	12	31.84 mm





Downloaded from Arrow.com.