ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at
www.onsemi.com

onsemi and onsemi and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi** product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

Downloaded from Arrow.com.

NTMFD4C87N

PowerPhase, Dual N-Channel SO8FL

30 V, High Side 20 A / Low Side 26 A

Features

- Co−Packaged Power Stage Solution to Minimize Board Space
- Minimized Parasitic Inductances
- Optimized Devices to Reduce Power Losses
- These Devices are Pb−Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- DC−DC Converters
- System Voltage Rails
- Point of Load




Figure 1. Typical Application Circuit





Figure 2. Typical Efficiency Performance POWERPHASEGEVB Evaluation Board


ON Semiconductor®

www.onsemi.com

$V_{(BR)DSS}$	$R_{DS(ON)}$ MAX	I_D MAX
Q1 Top FET 30 V	5.4 mΩ @ 10 V	20 A
	8.1 mΩ @ 4.5 V	
Q2 Bottom FET 30 V	3.1 mΩ @ 10 V	26 A
	4.3 mΩ @ 4.5 V	




PIN CONNECTIONS




(Bottom View)

MARKING DIAGRAM



DFN8
CASE 506CR



4C87N	= Specific Device Code
A	= Assembly Location
Y	= Year
W	= Work Week
ZZ	= Lot Traceability

ORDERING INFORMATION

See detailed ordering and shipping information on page 10 of this data sheet.

© Semiconductor Components Industries, LLC, 2015

Downloaded from Arrow.com.

MAXIMUM RATINGS (T_J = 25°C unless otherwise stated)

Parameter				Symbol	Value	Unit
Drain−to−Source Voltage			Q1	V_{DSS}	30	V
Drain−to−Source Voltage			Q2			
Gate−to−Source Voltage			Q1	V_{GS}	±20	V
Gate−to−Source Voltage			Q2			
Continuous Drain Current $R_{\theta JA}$ (Note 1)	Steady State	T_A = 25°C	Q1	I_D	15.4	A
		T_A = 85°C			11.1	
		T_A = 25°C	Q2		19.5	
		T_A = 85°C			14.1	
Power Dissipation RθJA (Note 1)		T_A = 25°C	Q1	P_D	1.89	W
			Q2			
Continuous Drain Current $R_{\theta JA} \le 10$ s (Note 1)		T_A = 25°C	Q1	I_D	21.0	A
		T_A = 85°C			15.1	
		T_A = 25°C	Q2		26.6	
		T_A = 85°C			19.2	
Power Dissipation $R_{\theta JA} \le 10$ s (Note 1)		T_A = 25°C	Q1	P_D	3.51	W
			Q2			
Continuous Drain Current $R_{\theta JA}$ (Note 2)		T_A = 25°C	Q1	I_D	11.7	A
		T_A = 85°C			8.5	
		T_A = 25°C	Q2		14.9	
		T_A = 85°C			10.7	
Power Dissipation $R_{\theta JA}$ (Note 2)		T_A = 25 °C	Q1	P_D	1.10	W
			Q2			
Pulsed Drain Current		T_A = 25°C t_p = 10 μs	Q1	I_{DM}	160	A
			Q2		260	
Operating Junction and Storage Temperature			Q1	T_J, T_{STG}	−55 to +150	°C
			Q2			
Source Current (Body Diode)			Q1	I_S	10	A
			Q2		10	
Drain to Source DV/DT				dV/dt	6	V/ns
Single Pulse Drain−to−Source Avalanche Energy (T_J = 25C, V_{DD} = 50 V, V_{GS} = 10 V, L = 0.1 mH, R_G = 25 Ω)		I_L = 20 A_{pk}	Q1	EAS	20	mJ
		I_L = 30 A_{pk}	Q2	EAS	45	
Lead Temperature for Soldering Purposes (1/8” from case for 10 s)				T_L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface−mounted on FR4 board using 1 sq−in pad, 2 oz Cu.
2. Surface−mounted on FR4 board using the minimum recommended pad size of 100 mm^2.

Downloaded from Arrow.com.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction−to−Ambient – Steady State (Note 3)	$R_{\theta JA}$	66.0	°C/W
Junction−to−Ambient – Steady State (Note 4)	$R_{\theta JA}$	113.7	
Junction−to−Ambient – (t ≤ 10 s) (Note 3)	$R_{\theta JA}$	35.6	

3. Surface−mounted on FR4 board using 1 sq−in pad, 2 oz Cu.
4. Surface−mounted on FR4 board using the minimum recommended pad size of 100 mm^2.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	FET	Symbol	Test Condition		Min	Typ	Max	Unit
OFF CHARACTERISTICS								
Drain−to−Source Breakdown Voltage	Q1	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 250 μA		30			V
	Q2				30			
Drain−to−Source Breakdown Voltage Temperature Coefficient	Q1	$V_{(BR)DSS}$ / T_J				15.8		mV / °C
	Q2					15.3		
Zero Gate Voltage Drain Current	Q1	I_{DSS}	V_{GS} = 0 V, V_{DS} = 24 V	T_J = 25°C			1	μA
				T_J = 125°C			10	
	Q2		V_{GS} = 0 V, V_{DS} = 24 V	T_J = 25°C			1	
Gate−to−Source Leakage Current	Q1	I_{GSS}	V_{GS} = 0 V, VDS = +20 V				100	nA
	Q2						100	
ON CHARACTERISTICS (Note 5)								
Gate Threshold Voltage	Q1	$V_{GS(TH)}$	V_{GS} = VDS, I_D = 250 μA		1.3		2.2	V
	Q2				1.3		2.2	
Negative Threshold Temperature Coefficient	Q1	$V_{GS(TH)}$ / T_J				5.0		mV / °C
	Q2					5.1		
Drain−to−Source On Resistance	Q1	$R_{DS(on)}$	V_{GS} = 10 V	I_D = 30 A		4.3	5.4	mΩ
			V_{GS} = 4.5 V	I_D = 18 A		6.5	8.1	
	Q2		V_{GS} = 10 V	I_D = 30 A		2.5	3.1	
			V_{GS} = 4.5 V	I_D = 30 A		3.4	4.3	
CAPACITANCES								
Input Capacitance	Q1	C_{ISS}	V_{GS} = 0 V, f = 1 MHz, V_{DS} = 15 V			1252		pF
	Q2					1939		
Output Capacitance	Q1	C_{OSS}				610		
	Q2					1055		
Reverse Capacitance	Q1	C_{RSS}				129		
	Q2					49		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	FET	Symbol	Test Condition	Min	Typ	Max	Unit
CHARGES, CAPACITANCES & GATE RESISTANCE							
Total Gate Charge	Q1	$Q_{G(TOT)}$	V_{GS} = 4.5 V, V_{DS} = 15 V; I_D = 30 A		10.9		nC
	Q2				13.8		
Threshold Gate Charge	Q1	$Q_{G(TH)}$			1.2		
	Q2				2.0		
Gate−to−Source Charge	Q1	Q_{GS}			3.4		
	Q2				5.5		
Gate−to−Drain Charge	Q1	Q_{GD}			5.4		
	Q2				3.6		
Total Gate Charge	Q1	$Q_{G(TOT)}$	V_{GS} = 10 V, V_{DS} = 15 V; I_D = 30 A		22.2		nC
	Q2				30.3		
Gate Resistance	Q1	R_G	T_A = 25°C		1.0		Ω
	Q2				1.0		
SWITCHING CHARACTERISTICS (Note 6)							
Turn−On Delay Time	Q1	$t_{d(ON)}$	V_{GS} = 4.5 V, V_{DS} = 15 V, I_D = 15 A, R_G = 3.0 Ω		8.9		ns
	Q2				10.6		
Rise Time	Q1	t_r			21.2		
	Q2				4.6		
Turn−Off Delay Time	Q1	$t_{d(OFF)}$			15.3		
	Q2				21		
Fall Time	Q1	t_f			4.4		
	Q2				4.9		
SWITCHING CHARACTERISTICS (Note 6)							
Turn−On Delay Time	Q1	$t_{d(ON)}$	V_{GS} = 10 V, V_{DS} = 15 V, I_D = 15 A, R_G = 3.0 Ω		6.7		ns
	Q2				8.1		
Rise Time	Q1	t_r			19.5		
	Q2				15		
Turn−Off Delay Time	Q1	$t_{d(OFF)}$			20.1		
	Q2				26.2		
Fall Time	Q1	t_f			2.8		
	Q2				3.1		
DRAIN−SOURCE DIODE CHARACTERISTICS							
Forward Voltage	Q1	V_{SD}	V_{GS} = 0 V, I_S = 10 A	T_J = 25°C	0.82		V
				T_J = 125°C	1.15		
	Q2		V_{GS} = 0 V, I_S = 10 A	T_J = 25°C	0.8		
				T_J = 125°C	1.10		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	FET	Symbol	Test Condition	Min	Typ	Max	Unit
DRAIN−SOURCE DIODE CHARACTERISTICS							
Reverse Recovery Time	Q1	t_{RR}	V_{GS} = 0 V, d_{IS}/d_t = 100 A/μs, I_S = 30 A		29.1		ns
	Q2				40.2		
Charge Time	Q1	ta			14.2		
	Q2				19.5		
Discharge Time	Q1	tb			14.6		
	Q2				20.6		
Reverse Recovery Charge	Q1	Q_{RR}			21		nC
	Q2				39		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS − Q1




Figure 3. On−Region Characteristics




Figure 4. Transfer Characteristics




Figure 5. On−Resistance vs. Gate−to−Source Voltage




Figure 6. On−Resistance vs. Drain Current and Gate Voltage




Figure 7. On−Resistance Variation with Temperature




Figure 8. Capacitance Variation

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS − Q1




Figure 9. Gate−to−Source and Drain−to−Source Voltage vs. Total Charge




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Resistive Switching Time Variation vs. Gate Resistance




Figure 12. Maximum Rated Forward Biased Safe Operating Area




Figure 13. Thermal Characteristics

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS − Q2




Figure 14. On−Region Characteristics




Figure 15. Transfer Characteristics




Figure 16. On−Resistance vs. V_{GS}




Figure 17. On−Resistance vs. Drain Current and Gate Voltage




Figure 18. On−Resistance Variation with Temperature




Figure 19. Drain−to−Source Leakage Current vs. Voltage

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS − Q2




Figure 20. Capacitance Variation




Figure 21. Gate−to−Source and Drain−to−Source Voltage vs. Total Charge




Figure 22. Diode Forward Voltage vs. Current

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS − Q2




Figure 23. Resistive Switching Time Variation vs. Gate Resistance




Figure 24. Maximum Rated Forward Biased Safe Operating Area




Figure 25. Thermal Characteristics

ORDERING INFORMATION


Device	Package	Shipping†
NTMFD4C87NT1G	DFN8 (Pb−Free)	1500 / Tape & Reel
NTMFD4C87NT3G	DFN8 (Pb−Free)	5000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

Downloaded from Arrow.com.


PACKAGE DIMENSIONS


DFN8 5x6, 1.27P PowerPhase FET
CASE 506CR
ISSUE C




NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSIONS b AND b1 APPLY TO PLATED TERMINAL AND ARE MEASURED BETWEEN 0.15 AND 0.25 MM FROM THE TIPS.
4. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
5. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
6. SEATING PLANE IS DEFINED BY THE TERMINALS. A1 IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.

	MILLIMETERS	
DIM	MIN	MAX
A	0.90	1.10
A1	0.00	0.05
b	0.40	0.60
b2	0.40	0.60
c	0.20	0.30
D	5.15 BSC	
D1	4.90	5.10
D2	3.70	3.90
D3	2.96	3.16
E	6.15 BSC	
E1	5.80	6.00
E2	2.37	2.57
E3	1.05	1.25
E4	1.36	1.56
e	1.27 BSC	
G	0.625 BSC	
G1	1.615 BSC	
h	−−−	12 °
L	0.34	0.59
L2	1.68	1.93





RECOMMENDED SOLDERING FOOTPRINT*



DIMENSION: MILLIMETERS

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

Downloaded from Arrow.com.

ON Semiconductor and ON are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5817−1050

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Downloaded from Arrow.com.