

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/7/17	


APPROVED: _____


DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT







NUT	BRASS	NONE
WASHER	S50C	GOLD
INSULATION	TEFLON	NONE
PIN	BRASS	GOLD
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
Nominal Impedance: 50 ohms
Frequency range: DC–18 GHz
Working voltage: 335 Volts max.
Proof voltage: 1,000 Volts
Temperature Rating:
Operating temperature: –65°C to +165°C
Environmental:
Lead free, RoHS compliant.

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	HR	11/7/17
CHECKED	AC	11/7/17
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
SMA JACK, END LUNCH, PCB

SIZE	PART NO.	REV.
X	RF2-114A-T-17-50-RP-G	-

REF: S00277T | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.