


 [Live Product Chat](#)



✓ Active

 [Add to Part List](#)

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Contact
- Contact Type = Receptacle
- Terminate To Wire
- Wire Insulation Diameter = 1.22 mm
- Wire Range = 0.05-0.15 [30-26] mm [AWG]

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings:

- [CONTACT, MOD V, RECEPTACLE, CRIMP SNAP-IN](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- [AMPMODU MOD IV, IV1/2, and V Receptacles and Housings](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

- Product Line Information

- Tooling

Product Type Features: • Product Type = Contact • Wire Insulation Diameter (mm [in]) = 1.22 [0.048] • Connector Series = Mod V • Wire Termination Type = Crimp • Applied Pressure = High Electrical Characteristics: • Voltage Rating (VAC) = 250 • Contact Current Rating (Amps.) = 3 • Termination Resistance (mΩ) = 12 • Insulation Resistance (MΩ) = 5,000 • Dielectric Withstanding Voltage (V) = 750 Termination Related Features: • Crimp Area Plating = Gold Flash Body Related Features: • Wire Range (mm [AWG]) = 0.05-0.15 [30-26]	Contact Related Features: • Contact Type = Receptacle • Contact Mating Area Plating Material = Gold (30) • Contact Material = Phosphor Bronze • Approved Standards = UL E28476, CSA LR7189 Industry Standards: • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Not relevant for lead free process • RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: • Terminate To = Wire • Operating Temperature (°C) = -65 - +105 Packaging Related Features: • Packaging Method = Loose Piece Other: • Brand = AMP
---	--