



Key Features

- 1. 400W Redundant power supplies
- 2. 4x 3.5" Hot-swap SAS2 (6Gb/s) / SATA Drive Bays
- 3. 1x Full-height AOC expansion slot
- 4. 4x 40x28mm high-efficiency fans (2 more optional; 6x fans maximum)
- 5. 1x Slim DVD/CD-ROM Drive (opt.)
- 6. Front USB/COM access
- 7. Applications: data center, appliance server, space critical application, industrial PC

Available Colors

Black

Product SKUs	<div>CSE-813MTQ-R400CB<ul style="list-style-type: none">SuperChassis 813MTQ-R400CB (Black)</div>
Form Factor	1U chassis support for motherboard sizes - Micro ATX 9.6" x 9.6" or ATX 12" x 10"
Processor Support	Supports dual, single Intel® / AMD processors
Dimensions	<div>Height<ul style="list-style-type: none">1.7" (43mm)Width<ul style="list-style-type: none">17.2" (437mm)Depth<ul style="list-style-type: none">19.85" (503mm)Gross Weight<ul style="list-style-type: none">33.5 lbs (15.2kg)Available Colors<ul style="list-style-type: none">Black</div>
Expansion Slots	1x Full-height AOC expansion slot
Drive Bays	<div>Hot-swap<ul style="list-style-type: none">4x 3.5" Hot-swap SAS2 (6Gb/s) / SATA drive baysSAS or enterprise SATA HDD only recommended</div>
SAS / SATA Backplane	1x SAS / SATA Backplane
Peripheral Drives	<div>DVD-ROM<ul style="list-style-type: none">Slim DVD-ROM drive (opt.)Others<ul style="list-style-type: none">Front USB/COM access</div>
Front Panel	<div>Buttons<ul style="list-style-type: none">Power On/Off buttonSystem Reset buttonLEDs<ul style="list-style-type: none">Power LEDHard drive activity LED2x Network activity LEDsSystem Overheat LED</div>
System Cooling	<div>Fans<ul style="list-style-type: none">4x 4cm 4-pin PWM fans2x additional fans optional; 6x fans total maximum</div>
Operating Environment (System)	<div>Operating Temperature Range<ul style="list-style-type: none">5°C - 35°C (41°F - 95°F)Non-Operating Temperature Range<ul style="list-style-type: none">-40°C - 70°C (-40°F - 158°F)Operating Relative Humidity Range<ul style="list-style-type: none">8% - 90% (non-condensing)Non-Operating Relative Humidity Range<ul style="list-style-type: none">5% - 95% (non-condensing)</div>
Power Supply	<div>400W (1+1) Redundant SuperCompact Short-depth AC-DC high-efficiency power supply with FMBus and I2C</div> <div>AC Input<ul style="list-style-type: none">400W: 100-240 V, 50-60 Hz, 6-3 AmpDC Output +5V standby<ul style="list-style-type: none">3 AmpDC Output +12V<ul style="list-style-type: none">33 AmpWith Power Distributor<ul style="list-style-type: none">+5V: 25 Amp+3.3V: 25 Amp-12V: 0.6 Amp</div>
Regulatory (Power Supply)	<div>Power Supply Safety / EMC<ul style="list-style-type: none">USA - UL listed, FCCCanada - CUL listedEurope/CE MarkEN 60950/IEC 60950-Compliant</div>

[See Parts List](#)