




SLR-342 Series

Features

- Viewing angle 2θ 1/2 : 40°

Color Type V D Y M

Specifications


Viewing angle 2θ 1/2 : 40°: Standard

Part No.	Chip Structure	Emitting Color	Absolute Maximum Ratings (Ta=25℃)						Electrical and Optical Characteristics (Ta=25℃)												
			Power Dissipation Pd(mW)	Forward Current If(mA)	Peak Forward Current Ifp(mA)	Reverse Voltage Vr(V)	Operating Temperature Topr(℃)	Storage Temperature Tstg(℃)	Forward Voltage V _f Typ.(V)	Reverse Current I _r Max. (μA)	Reverse Current I _r Typ.(V)	Dominant Wavelength λ D Typ.(nm)	Luminous Intensity I _v Min.(mcd)	Luminous Intensity I _v Typ.(mcd)	Luminous Intensity I _v Max.(mcd)						
■ SLR-342VC	GaAsP on GaP	Red							2.0				630		9.0	25					
■ SLR-342DC		Orange	60	20									605								
■ SLR-342YC		Yellow							2.1				587		5.6	16					
■ SLR-342MC	GaP	Yellowish Green	75	25	60*	3	-25 to +85	-30 to +100	10	10	10	3	572	10	9.0	25	10				
■ SLR-342VR	Red														630						
■ SLR-342DU	GaAsP on GaP	Orange	60	20															605		5.6
■ SLR-342YY		Yellow																587		3.6	10
■ SLR-342MG	GaP	Yellowish Green	75	25														2.1			


* SLR-342 series are only available as formed lead types. SLR-343 series are recommended for bulk, and straight lead types.

* :Duty1/5, 200Hz


Dimensions



Recommended Solder Pattern




Viewing Angle




Electrical Characteristics Curves


Forward Current-Forward Voltage




Luminous Intensity-Atmosphere Temperature



Luminous Intensity-Forward Current



Derating



Packing Specification

www.rohm.com
© 2010 ROHM Co., Ltd.
Downloaded from Arrow.com.

www.rohm.com
© 2010 ROHM Co., Ltd.

www.rohm.com
© 2010 ROHM Co., Ltd. All rights reserved.

www.rohm.com
© 2010 ROHM Co., Ltd.

www.rohm.com
© 2010 ROHM Co., Ltd.

www.rohm.com
© 2010 ROHM Co., Ltd. All rights reserved.

www.rohm.com
© 2010 ROHM Co., Ltd.

www.rohm.com
© 2010 ROHM Co., Ltd.

www.rohm.com
© 2010 ROHM Co., Ltd. All rights reserved.

www.rohm.com
© 2010 ROHM Co., Ltd.

www.rohm.com
© 2010 ROHM Co., Ltd.

www.rohm.com
© 2010 ROHM Co., Ltd. All rights reserved.

www.rohm.com
© 2010 ROHM Co., Ltd.

www.rohm.com
© 2010 ROHM Co., Ltd.



- www.rohm.com
© 2010 ROHM Co., Ltd. All rights reserved.

www.rohm.com
© 2010 ROHM Co., Ltd. All rights reserved.

www.rohm.com 3/3 2010

Notes

No copying or reproduction of this document, in part or in whole, is permitted without the consent of ROHM Co.,Ltd.

The content specified herein is subject to change for improvement without notice.

The content specified herein is for the purpose of introducing ROHM's products (hereinafter "Products"). If you wish to use any such Product, please be sure to refer to the specifications, which can be obtained from ROHM upon request.

Examples of application circuits, circuit constants and any other information contained herein illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

Great care was taken in ensuring the accuracy of the information specified in this document. However, should you incur any damage arising from any inaccuracy or misprint of such information, ROHM shall bear no responsibility for such damage.

The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM and other parties. ROHM shall bear no responsibility whatsoever for any dispute arising from the use of such technical information.

The Products specified in this document are intended to be used with general-use electronic equipment or devices (such as audio visual equipment, office-automation equipment, communication devices, electronic appliances and amusement devices).

The Products specified in this document are not designed to be radiation tolerant.

While ROHM always makes efforts to enhance the quality and reliability of its Products, a Product may fail or malfunction for a variety of reasons.

Please be sure to implement in your equipment using the Products safety measures to guard against the possibility of physical injury, fire or any other damage caused in the event of the failure of any Product, such as derating, redundancy, fire control and fail-safe designs. ROHM shall bear no responsibility whatsoever for your use of any Product outside of the prescribed scope or not in accordance with the instruction manual.

The Products are not designed or manufactured to be used with any equipment, device or system which requires an extremely high level of reliability the failure or malfunction of which may result in a direct threat to human life or create a risk of human injury (such as a medical instrument, transportation equipment, aerospace machinery, nuclear-reactor controller, fuel-controller or other safety device). ROHM shall bear no responsibility in any way for use of any of the Products for the above special purposes. If a Product is intended to be used for any such special purpose, please contact a ROHM sales representative before purchasing.

If you intend to export or ship overseas any Product or technology specified herein that may be controlled under the Foreign Exchange and the Foreign Trade Law, you will be required to obtain a license or permit under the Law.



Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

<http://www.rohm.com/contact/>