










SLB Series

(with p.c. board stand-off bracket)

Miniature Slide Switches

SPECIFICATIONS	FEATURES
Contact ratings: 300 mA at 125 VAC or 30 VDC Initial contact resistance: 20 milliohms max. Insulation resistance: 100 megohms min. at 500 VDC Dielectric strength: 500 volts RMS for 1 minute Electrical life: 10,000 cycles min. Operating temperature range: -20°C to +85°C Actuation force: 220g ± 100g Solder heat resistance: 260°C max. for 3 seconds Solvent washing permissible	- Miniature compact size. - Wash-through open frame construction. - Positive spring loaded ball detent mechanism. - Epoxy sealed terminals.
	MATERIALS
	Contacts & terminals: Silver plated Frame: Zinc plated steel Actuator: Thermoplastic Base: Phenolic laminated sheet Terminal seal: Epoxy

MODEL NO. SLB12814	1P2T   
MODEL NO. SLB1281R5	1P2T   
MODEL NO. SLB1370	1P3T   














SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

SLB Series

(with p.c. board stand-off bracket)

Miniature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE













MODEL NO. SLB13814  VERTICAL ACTUATOR	1P3T    SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLB1381R5  RIGHT ANGLE ACTUATOR	1P3T    SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLB1470  VERTICAL ACTUATOR	1P4T    SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLB1570  VERTICAL ACTUATOR	1P5T    SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT

SLB Series

(with p.c. board stand-off bracket)

Miniature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

MODEL NO. SLB22814	2P2T  VERTICAL ACTUATOR SCHEMATIC  ● = COMMON MECHANICAL OUTLINE  P.C. BOARD LAYOUT 
MODEL NO. SLB2281R5	2P2T  RIGHT ANGLE ACTUATOR SCHEMATIC  ● = COMMON MECHANICAL OUTLINE  P.C. BOARD LAYOUT 
MODEL NO. SLB23814	2P3T  VERTICAL ACTUATOR SCHEMATIC  MECHANICAL OUTLINE  P.C. BOARD LAYOUT 
MODEL NO. SLB2381R5	2P3T  RIGHT ANGLE ACTUATOR SCHEMATIC  MECHANICAL OUTLINE  P.C. BOARD LAYOUT 










SLB Series

(with thru- p.c. board hole mounting bracket)

Miniature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

SPECIFICATIONS	FEATURES
Contact ratings: 300 mA at 125 VAC or 30 VDC Initial contact resistance: 20 milliohms max. Insulation resistance: 100 megohms min. at 500 VDC Dielectric strength: 500 volts RMS for 1 minute Electrical life: 10,000 cycles min. Operating temperature range: -20°C to +85°C Actuation force: 220g ± 100g Solder heat resistance: 260°C max. for 3 seconds Solvent washing permissible	- Miniature compact size. - Wash-through open frame construction. - Positive spring loaded ball detent mechanism. - Epoxy sealed terminals.
	MATERIALS
	Contacts & terminals: Silver plated Frame: Zinc plated steel Actuator: Thermoplastic Base: Phenolic laminated sheet Terminal seal: Epoxy






MODEL NO.	1P2T
SLB12804	
 VERTICAL ACTUATOR	 ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO.	1P2T
SLB124145	
 VERTICAL ACTUATOR	 ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO.	1P2T
SLB1240R45	
 RIGHT ANGLE ACTUATOR	 ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT

SLB Series

(with thru- p.c. board hole mounting bracket)

Miniature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE







MODEL NO. SLB1280R5  RIGHT ANGLE ACTUATOR	1P2T .126 (3.20) TRAVEL/THROW  SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLB1250R8  RIGHT ANGLE ACTUATOR	1P2T .098 (2.50) TRAVEL/THROW  SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLB1370R  RIGHT ANGLE ACTUATOR	1P3T .090 (2.30) TRAVEL/THROW  SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLB13804  VERTICAL ACTUATOR	1P3T .126 (3.20) TRAVEL/THROW  SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT

SLB Series

(with thru-p.c. board hole mounting bracket)

Miniature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

MODEL NO. SLB134145  VERTICAL ACTUATOR	1P3T .079 (2.00) TRAVEL/THROW  SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLB1340R45  RIGHT ANGLE ACTUATOR	1P3T .079 (2.00) TRAVEL/THROW  SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLB1380R5  RIGHT ANGLE ACTUATOR	1P3T .126 (3.20) TRAVEL/THROW  SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT
MODEL NO. SLB1470R  RIGHT ANGLE ACTUATOR	1P4T .090 (2.30) TRAVEL/THROW  SCHEMATIC MECHANICAL OUTLINE P.C. BOARD LAYOUT

SLB Series


(with thru-p.c. board hole mounting bracket)

Miniature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE


MODEL NO.

SLB1570R




RIGHT ANGLE ACTUATOR


1P5T



SCHEMATIC



MECHANICAL OUTLINE



P.C. BOARD LAYOUT


MODEL NO.

SLB22804




VERTICAL ACTUATOR


2P2T



SCHEMATIC



MECHANICAL OUTLINE



P.C. BOARD LAYOUT


MODEL NO.

SLB224145




VERTICAL ACTUATOR


2P2T



SCHEMATIC



MECHANICAL OUTLINE



P.C. BOARD LAYOUT


MODEL NO.

SLB2240R45




RIGHT ANGLE ACTUATOR


2P2T



SCHEMATIC



MECHANICAL OUTLINE
















P.C. BOARD LAYOUT

SLB Series

(with thru-p.c. board hole mounting bracket)
Miniature Slide Switches

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE

MODEL NO. SLB2280R5  RIGHT ANGLE ACTUATOR	2P2T  ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO. SLB23804  VERTICAL ACTUATOR	2P3T   MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO. SLB234145  VERTICAL ACTUATOR	2P3T  ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT
MODEL NO. SLB2340R45  RIGHT ANGLE ACTUATOR	2P3T  ● = COMMON  MECHANICAL OUTLINE  P.C. BOARD LAYOUT