

NOTES:

MATERIAL

1. Insulator Material: PBT+30%GF(UL94V-0), Grey
2. Contact Material : Brass
3. Contact Plating :
AWHW xxG-0202-T: Gold flash/Tin Over Ni
AWHW xxG-0102-T: 30u"Au/Tin Over Ni
ELECTRICAL



- 1.Current Rating : 3AMP
- 2.Withstand Voltage : 500V AC/Minute
- 3.Contact Resistance : 20mΩ max
- 4.Insulation Resistance: 1000MΩ min

ENVIRONMENTAL

- 1.Operation Temperature: -40°C to +105°C
2.Packing : Tray packing

Order information:

xx : 06,08,10,12,14,16,18,20,24
26,30,34,40,50,60,64




| Dimenslon antltheses llt | |
|--------------------------|------|
| NO. Pin | L |
| 6P-8P | 4.00 |
| 10P-64P | 4.40 |

RoHS compliant
Unit: mm



File No.: E198287

| | | | | | | | | | | | |
|-----------|-------|-----|-------------------------|------------|--------|---|------------|--------------|---|--|--------------|
| Scale | Free | | | | | Date | Name | Customer-No. | | | |
| TOLERANCE | | | | | | Drawn | 25.01.2006 | Alex | | | |
| X.X | ±0.40 | ④ | Add UL file no. | 12.12.2013 | Amy | Approved | 12.12.2013 | Amy | ASSMANN WSW-No. AWHW xxG-0202-T AWHW xxG-0102-T | | |
| X.XX | ±0.25 | | | | | | | | | | |
| X.XXX | ±0.15 | ③ | Add the plating Au 30u" | 23.10.2013 | Winnie | | | | | | |
| DIM | TOL | ② | Update | 29.06.2009 | Dean |  | | | Drawing-No. | | |
| Angle | ±3° | | | | | | | | ASS 2314 CO | | rev04 |
| | | ① | Drawn | 25.01.2006 | Alex | | | | | | |
| | | Id. | Modification | Date | Name | | | | Replace | | Sheet 1/2 |

