




The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant or per IEC 61249-2-21 for Halogen-Free compliant.



1. HOUSING: LCP (E130i), UL 94V-0, COLOR- BLACK
2. CONTACT: BRONZE (C7035-TM06), 0.20mm THICKNESS, SELECTIVE GOLD PLATED
ON CONTACT AREA, 100μ" MATTE TIN PLATED ON SOLDERING TAIL,
50μ" MIN. NICKEL UNDER-PLATED OVERALL
3. SHELL: STAINLESS STEEL (SUS304), 0.25mm THICKNESS,
60μ"~150 μ" MIN. MATTE TIN PLATED ON SOLDERING TAILS OVER 50μ" MIN.
NICKEL PLATED OVERALL
4. INSERT-MOLD/ REAR GUIDE: LCP (E130i), UL 94V-0, COLOR- BLACK
5. PACKAGE DRAWING REFER TO PKS-G13AP001HR; PRODUCT SPECIFICATION: PS-
6.  MUST BE MEASURED BY FAI.
7. MAJOR DIMENSION  SHOULD BE CONTROLLED BY QIP.
8.  MUST BE CONTROLLED BY SPC.
9. THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS MATERIALS PER DIRECTIVE
2011/65/EC FOR ROHS AND PER IEC 61249-2-21 FOR HALOGEN FREE COMPLIANT.

TERMINAL STYLE
1: SMT TYPE

TOLERANCE		DRAWN APPROVALS		DATE	EXTREMEPORT FLASH 8X CONN. RECEPTACLE, R/A HEIGHT 4.5mm			Amphenol®						
X. ±0.20 X.X ±0.15 X.XX ±0.10 X.XXX ±0.05		DESIGNED	Sondra Sang	07/26/2018				Amphenol Corporation						
		CHECKED	Chenny Yeh	07/26/2018				Amphenol Taiwan Corporation						
		APPROVED	Hank Hsu	07/26/2018										
ANGULAR ±1°							UNIT	mm	SIZE	A3	PART No.	G13A 501X 12X 3X HR		
UNLESS OTHERWISE SPECIFIED		DWG TYPE	ENG DWG	PROJECT CODE	TXXX	SCALE		NA	SHEET	1 OF 1	DWG No.	E-G13A501X12X3XHR	REV.	AX1