CUI Devices is now Same Sky! Learn More

same sky

Additional Resources: Product Page

SERIES: MD-S | DESCRIPTION: MINI DIN CONNECTOR

FEATURES

- PCB mount
- right angle
- non-shielded



RoHS

PART NUMBER KEY

MD - XX S

Base Number

Pin Options
30* = 3 pins
40 = 4 pins
50* = 5 pins
60 = 6 pins
70 = 7 pins
80 = 8 pins
90 = 9 pins

Notes: *Discontinued models MD-30S & MD-50S

SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
rated input voltage			100 12		Vac Vdc
rated input current	at 100 Vac at 12 Vdc			1 2	A A
contact resistance				30	mΩ
insulation resistance	at 250 Vdc	50			MΩ
voltage withstand				250	Vac
insertion force		0.8		6.0	kg
withdrawal force		0.8		4.5	kg
operating temperature		-40		85	°C
life			1,000		cycles
flammability rating	UL94V-0				
RoHS	yes				

SOLDERABILITY


parameter	conditions/description	min	typ	max	units
wave soldering	for 10 seconds max	235		260	°C
hand soldering	for 5±1 seconds	240	245	250	°C

Downloaded from Arrow.com.


MECHANICAL DRAWINGS (MD-30S, MD-40S, MD-50S)


units: mm
tolerance: ±0.3 mm
PCB: ±0.1 mm
unless otherwise noted

ITEM	DESCRIPTION	MATERIAL	PLATING/COLOR
1	body	PBT (UL94V-0)	black
2	cover	PBT (UL94V-0)	black
3	earth terminal	brass	tin
4	terminals	phosphor bronze	silver




MD-40S







Recommended PCB Layout
Top View
(Date Codes prior to 03/03/2022)

MD-30S







Recommended PCB Layout
Top View



Recommended PCB Layout
Top View
(Date Codes after 03/03/2022)

MD-50S






Recommended PCB Layout
Top View


Downloaded from Arrow.com.

MECHANICAL DRAWINGS (MD-60S, MD-70S, MD-80S)


units: mm
tolerance: ±0.3 mm
PCB: ±0.1 mm
unless otherwise noted


ITEM	DESCRIPTION	MATERIAL	PLATING/COLOR
1	body	PBT (UL94V-0)	black
2	cover	PBT (UL94V-0)	black
3	earth terminal	brass	tin
4	terminals	phosphor bronze	silver






MD-60S






Recommended PCB Layout
Top View
(Date Codes prior to 03/03/2022)




Recommended PCB Layout
Top View
(Date Codes after 03/03/2022)

MD-70S







Recommended PCB Layout
Top View
(Date Codes prior to 03/03/2022)




Recommended PCB Layout
Top View
(Date Codes after 03/03/2022)

MD-80S





Recommended PCB Layout
Top View
(Date Codes prior to 03/03/2022)




Recommended PCB Layout
Top View
(Date Codes after 03/03/2022)


Downloaded from Arrow.com.


MECHANICAL DRAWING (MD-90S)

units: mm
tolerance: ±0.3 mm
PCB: ±0.1 mm
unless otherwise noted


ITEM	DESCRIPTION	MATERIAL	PLATING/COLOR
1	body	PBT (UL94V-0)	black
2	cover	PBT (UL94V-0)	black
3	earth terminal	brass	tin
4	terminals	phosphor bronze	silver







Recommended PCB Layout
Top View
(Date Codes prior to 03/03/2022)



Recommended PCB Layout
Top View
(Date Codes after 03/03/2022)

Downloaded from Arrow.com.

REVISION HISTORY

rev.	description	date
1.0	initial release	02/23/2006
1.01	new template applied	02/16/2012
1.02	housing updates	03/29/2012
1.03	updated datasheet	08/25/2017
1.04	discontinued models MD-30S and MD-50S, brand update	10/08/2019
1.05	updated housing	12/12/2019
1.06	updated PCB footprints	09/01/2020
1.07	modified design, changed factory	02/18/2022
1.08	logo, datasheet style update	08/05/2022
1.09	CUI Devices rebranded to Same Sky	09/12/2024

The revision history provided is for informational purposes only and is believed to be accurate.

same sky

Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com

Downloaded from Arrow.com.