


39611600440 - 396 Series



Series: 396

Fuse 396 Datasheet

- Features:
- Lead free
 - Reduced PCB space requirements
 - Direct solderable or plug-in versions
 - Internationally approved
 - Low internal resistance
 - Shocksafe casing
 - Vibration resistance
 - Halogen free

Click on part number below for individual TC curve files.

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

Feedback

Electrical Characteristics	Technical Resources	Environmental Info
Property (Mouseover for details)	Value	
Ampere Rating (A)	1.6	
Nominal Melting I ² T (A ² sec)	5.2	
Interrupting Rating	100A@125VAC	
Min Operating Temp °C	-40	
Max Operating Temp (°C)	85	
Moisture Sensitivity Level	MIL-STD-202 Method 106	
Nominal Power Dissipation (W)	210	
Nominal Voltage Drop (mV)	130	
Nominal Cold Resistance (Ohms)	0.0502	
Opening	Slo-Blo/Time Lag (T)/Time Delay	
Package Size	TE5 (8.5x8mm)	
VAC (V)	125	

Connect with Littelfuse
Sign up to receive special offers and news

For more details about how we use your information, check our [Privacy Statement](#).

- About Littelfuse**
- About Littelfuse
 - Conflict Free Statement
 - History
 - Investor Relations
 - Legal
 - Press Room
 - Privacy Statement
 - Supply Chain Transparency
 - Website Feedback

- Explore Littelfuse**
- Capabilities Brochures
 - Careers
 - Check Distributor Stock
 - Competitor Cross Reference
 - Industries
 - Order Samples
 - Products
 - Services

- Technical Resources**
- Application Designs
 - Education
 - FAQs
 - iDesign™
 - Littelfuse University
 - Product Catalogs
 - Quality Documents
 - Technical Documents