






REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
C	UPDATE THE TAPE AND PACKAGING	MAY25/22	KELVIN.T
D	ADD DIMS TO THE PACKAGING TAPE	JUN09/22	KELVIN.T




RECOMMENDED P.C.B LAYOUT
(COMPONENT SIDE OF BOARD)
TOLERANCE:±0.05[.002]



- NOTE:**
- MATERIALS:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
FLAMMABILITY RATING UL94 V-0,
COLOUR: BLACK
CONTACTS: PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD PLATING
ON MATING SURFACES;
100u" [2.54 MICRONS] MIN. MATTE TIN
ON SOLDER TAILS;
50u" [1.27 MICRONS] MIN. NICKEL
UNDERPLATING OVERALL.
SOLDER BRACKET: STAINLESS STEEL
PLATING: MATTE TIN OVER ALL
 - COPLANARITY SPECIFICATION:
THE MAX GAP BETWEEN ALL TERMINAL TAILS &
SOLDER BRACKET IS 0.10[.004] MAX.

AMPHENOL PART NUMBER: RJE23-166-0X13-T

- GOLD PLATING OPTION
- 1= 6u"[0.15 MICRONS] GOLD PLATING
 - 2= 15u"[0.38 MICRONS] GOLD PLATING
 - 3= 30u"[0.76 MICRONS] GOLD PLATING
 - 4= 50u"[1.27 MICRONS] GOLD PLATING



UNLESS SPECIFIED OTHERWISE	DRAWN	JUSTIN.F	JUN13/14
PRIMARY UNITS MILLIMETERS	CHECKED	L.CHAN	JUN13/14
SECONDARY INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE ±0.38	ENG. REL. NO.		
2 DECIMAL PLACES ±0.25	REF.		
3 DECIMAL PLACES ±0.13	THIRD ANGLE PROJECTION		
ANGULAR DEGREES ±1.0°			

Amphenol Canada Corp.

Commercial Products

TOP ENTRY MODULAR JACK,
SURFACE MOUNT 6 POSITIONS, 6
CONTACTS, WITH MYLAR TAPE,

P-RJE23-166-0X13-T

DO NOT SCALE DRAWING

DWG. NO.

CODE ID NO. 03554

SCALE: 5:1

SHEET 1 OF 2

REV D

