

Field Effect Transistor - N-Channel, Enhancement Mode

BS270

General Description

These N-Channel enhancement mode field effect transistors are produced using onsemi's proprietary, high cell density, DMOS technology. These products have been designed to minimize on-state resistance while provide rugged, reliable, and fast switching performance. They can be used in most applications requiring up to 500 mA DC. These products are particularly suited for low voltage, low current applications such as small servo motor control, power MOSFET gate drivers, and other switching applications.

Features

- 400 mA, 60 V. $R_{DS(ON)} = 2 \Omega$ @ $V_{GS} = 10 V$
- High Density Cell Design for Low $R_{DS(ON)}$
- Voltage Controlled Small Signal Switch
- Rugged and Reliable
- High Saturation Current Capability
- These are Pb-Free Devices


ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ C$ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{DSS}	Drain-Source Voltage	60	V
V_{DGR}	Drain-Gate Voltage ($R_{GS} \leq 1 M\Omega$)	60	V
V_{GSS}	Gate-Source Voltage – Continuous – Non Repetitive ($t_p < 50 \mu s$)	± 20 ± 40	V
I_D	Drain Current – Continuous – Pulsed	400 2000	mA
P_D	Maximum Power Dissipation Derate above $25^\circ C$	625 5	mW mW/ $^\circ C$
T_J, T_{STG}	Operating and Storage Temperature Range	-55 to 150	$^\circ C$
T_L	Maximum Lead Temperature for Soldering Purposes, $1/16"$ from Case for 10 Seconds	300	$^\circ C$


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	200	$^\circ C/W$




TO-92 3 4.825x4.76
CASE 135AN




TO-92 3 4.83x4.76 LEADFORMED
CASE 135AR

MARKING DIAGRAM



BS270 = Device Code
A = Assembly Site
L = Wafer Lot Number
YW = Assembly Start Week



ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

BS270

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Condition	Min	Typ	Max	Unit
--------	-----------	----------------	-----	-----	-----	------

OFF CHARACTERISTICS

BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS} = 0\text{ V}, I_D = 10\text{ }\mu\text{A}$	60	–	–	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 60\text{ V}, V_{GS} = 0\text{ V}$	–	–	1	μA
		$V_{DS} = 60\text{ V}, V_{GS} = 0\text{ V}, T_J = 125^\circ\text{C}$	–	–	500	μA
I_{GSSF}	Gate – Body Leakage, Forward	$V_{GS} = 20\text{ V}, V_{DS} = 0\text{ V}$	–	–	10	nA
	Gate – Body Leakage, Reverse	$V_{GS} = -20\text{ V}, V_{DS} = 0\text{ V}$	–	–	-10	nA

ON CHARACTERISTICS (Note 1)

$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250\text{ }\mu\text{A}$	1	2.1	2.5	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS} = 10\text{ V}, I_D = 500\text{ mA}$	–	1.2	2	Ω
		$V_{GS} = 10\text{ V}, I_D = 500\text{ mA}, T_J = 125^\circ\text{C}$	–	2	3.5	
		$V_{GS} = 4.5\text{ V}, I_D = 75\text{ mA}$	–	1.8	3	
$V_{DS(ON)}$	Drain-Source On-Voltage	$V_{GS} = 10\text{ V}, I_D = 500\text{ mA}$	–	0.6	1	V
		$V_{GS} = 4.5\text{ V}, I_D = 75\text{ mA}$	–	0.14	0.225	
$I_{D(ON)}$	On-State Drain Current	$V_{GS} = 10\text{ V}, V_{DS} \geq 2\text{ }V_{DS(on)}$	2000	2700	–	mA
		$V_{GS} = 4.5\text{ V}, V_{DS} \geq 2\text{ }V_{DS(on)}$	400	600	–	
g_{FS}	Forward Transconductance	$V_{DS} \geq 2\text{ }V_{DS(on)}, I_D = 200\text{ mA}$	100	320	–	mS

DYNAMIC CHARACTERISTICS

C_{iss}	Input Capacitance	$V_{DS} = 25\text{ V}, V_{GS} = 0\text{ V}, f = 1.0\text{ MHz}$	–	20	50	pF
C_{oss}	Output Capacitance		–	11	25	pF
C_{rss}	Reverse Transfer Capacitance		–	4	5	pF

SWITCHING CHARACTERISTICS (Note 1)

t_{on}	Turn-On Time	$V_{DD} = 30\text{ V}, I_D = 500\text{ mA}, V_{GS} = 10\text{ V}, R_{GEN} = 25\text{ }\Omega$	–	–	10	ns
t_{off}	Turn-Off Time		–	–	10	ns

DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS

I _S	Maximum Continuous Drain-Source Diode Forward Current	–	–	400	mA		
I _{SM}	Maximum Pulsed Drain-Source Diode Forward Current	–	–	2000	mA		
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} = 0 V, I _S = 400 mA (Note 1)		–	0.88	1.2	V

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Pulse Test: Pulse Width $\leq 300\text{ }\mu\text{s}$, Duty Cycle $\leq 2.0\%$.

TYPICAL ELECTRICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. On-Resistance Variation with Gate Voltage and Drain Current




Figure 3. On-Resistance Variation with Temperature




Figure 4. On-Resistance Variation with Drain Current and Temperature




Figure 5. Transfer Characteristics




Figure 6. Gate Threshold Variation with Temperature

TYPICAL ELECTRICAL CHARACTERISTICS (continued)




Figure 7. Breakdown Voltage Variation with Temperature




Figure 8. Body Diode Forward Voltage Variation with Current and Temperature




Figure 9. Capacitance Characteristics




Figure 10. Gate Charge Characteristics




Figure 11. Switching Test Circuit




Figure 12. Switching Waveforms

TYPICAL ELECTRICAL CHARACTERISTICS (continued)




Figure 13. Maximum Safe Operating Area




Figure 14. Transient Thermal Response Curve

ORDERING INFORMATION

Part Number	Package	Shipping
BS270	TO-92, Case 135AN (Pb-Free)	10000 Units / Bulk
BS270-D74Z	TO-92, Case 135AR (Pb-Free)	2000 Units / Fan-Fold

BS270

REVISION HISTORY


Revision	Description of Changes	Date
4	Data Sheet Discontinued.	2/11/2025

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.

DISCONTINUED
THIS DEVICE IS NOT AVAILABLE
PLEASE CONTACT YOUR onsemi
REPRESENTATIVE FOR INFORMATION

TO-92 3 4.825x4.76
CASE 135AN
ISSUE O

DATE 31 JUL 2016



NOTES: UNLESS OTHERWISE SPECIFIED




- A) DRAWING WITH REFERENCE TO JEDEC TO-92 RECOMMENDATIONS.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DRAWING CONFORMS TO ASME Y14.5M-2009.

DOCUMENT NUMBER:	98AON13880G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-92 3 4.825X4.76	PAGE 1 OF 1

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

TO-92 3 4.83x4.76 LEADFORMED
CASE 135AR
ISSUE O

DATE 30 SEP 2016



NOTES: UNLESS OTHERWISE SPECIFIED

- A) DRAWING WITH REFERENCE TO JEDEC TO-92 RECOMMENDATIONS.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.
- C) DRAWING CONFORMS TO ASME Y14.5M-1994

DOCUMENT NUMBER:	98AON13879G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TO-92 3 4.83X4.76 LEADFORMED	PAGE 1 OF 1

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

