

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0399400204

Status:

Active

Overview:

Eurostyle Terminal Blocks

Description:

5.08mm Pitch Beau EuroMate Pluggable PCB Terminal Block, Dual Level, 90° Wire Entry, 4 Circuits

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-39940-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E48521

General

Product Family

Series

Application

Comments

Component Type

Overview

Product Name

Type

UPC

Terminal Blocks

39940

N/A

Gold plating available

Plug

Eurostyle Terminal Blocks

EuroMate Pluggable

Euro Block

800756371894

Physical

Circuits (Loaded)

Color - Resin

Entry Angle

Flammability

Lock to Mating Part

Material - Resin

Number of Rows

Orientation

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

Wire Size mm²

4

Black

Horizontal

94V-0

None

Nylon

2

Vertical

No

5.08mm

5.08mm

Yes

No

130°C

Screw or Lug

12, 14, 16, 18, 20, 22

0.50-2.50

Electrical

Current - Maximum per Contact

Voltage - Maximum

15.0A

300V

Material Info

Engineering Number

940804


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-39940-001-001

SD-39940-004



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contained Per -

D(2020)4578-DC (25

June 2020)

pentacosafuorotridecanoic

acid

1,2-

Benzenedicarboxylic

acid, dihexyl ester,

bra

Terphenyl,

hydrogenated

2-(2H-benzotriazol-2-

yl)-4-(tert-butyl)-6-

(sec-b

2-(2H-benzotriazol-2-

yl)-4,6-

ditertpentylphenol

2-ethylhexyl 10-

ethyl-4,4-dioctyl-7-

oxo-8-oxa-3,

sodium

peroxometaborate

Ammonium-

pentadecafluorooctanoate

disodium 4-

amino-3-[[4'-[(2,4-

diaminophenyl)azo]

1,3-propanesultone

1-vinylimidazole

1,2-diethoxyethane

disodium 3,3'-[[1,1'-

biphenyl]-4,4'-

diylbis(azo)

dodecamethylcyclhexasiloxane

Octanoic acid,

2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-

pen

Dipentyl phthalate

furan

4-o-tolylazo-o-toluidine
ethylene thiourea
4-methyl-m-phenylenediamine
o-toluidine
butyl 4-hydroxybenzoate
phenanthrene
dicyclohexyl phthalate
p-(1,1-dimethylpropyl)phenol
N-methylacetamide
1,2-Benzenedicarboxylic acid, dipentyl ester, br
Perfluorohexane-1-sulphonic acid and its salts
5-sec-butyl-2-(2,4-dimethylcyclohex-3-en-1-yl)-5
1,2-benzenedicarboxylic acid, di-C6-10-alkyl est
reaction mass of 2-ethylhexyl 10-ethyl-4,4-dioct
Cadmium sulphate
Bisphenol-A
Methylhexahydrophthalic anhydride
Perfluorononan-1-oic acid
(2,2,3,3,4,4,5,5,6,6,7
Reaction
products of 1,3,4-thiadiazolidine-2,5-d
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Pyrene
Perfluorobutane sulfonic acid (PFBS) and its sal
Tris(4-nonylphenyl, branched and linear) phosphi
Nonadecafluorodecanoic acid (PFDA) and its sodiu
4-Nonylphenol, branched and linear, ethoxylated
Trixylyl phosphate
4-Nonylphenol, branched and linear
[substances w
Zirconia
Aluminosilicate
Refractory Ceramic Fibr
Aluminosilicate
Refractory Ceramic Fibres

4,4'-Oxydianiline and
its salts
Boric acid
Disodium tetraborate
n-pentyl-
isopentylphthalate
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
2-benzyl-2-
dimethylamino-4-
morpholinobutyropheno
2-methyl-1-(4-
methylthiophenyl)-2-
morpholinoprop
pentazinc chromate
octahydroxide
trilead diarsenate
arsenic acid
potassium
hydroxyoctaoxodizincatedichromate(1-)
1,2-
Benzenedicarboxylic
acid, di-C6-8-
branched a
1,2,3-trichloropropane
N-methyl-2-
pyrrolidone
1,2-
Benzenedicarboxylic
acid, di-C7-11-
branched
2-ethoxyethyl acetate
Cobalt sulphate
Cobalt-dinitrate
Carbonic acid,
cobalt(2+) salt (1:1)
2-ethoxyethanol
trichloroethylene
Boric acid, disodium
salt, hydrate
potassium dichromate
potassium chromate
Pitch, coal tar, high-
temp.
Lead chromate
molybdate sulfate red
lead chromate
Anthracene oil,
anthracene-low;
Anthracene Oil F
lead hydrogen
arsenate
bis(2-ethylhexyl)
phthalate (DEHP)
diarsenic trioxide
dibutyl phthalate
(DBP)
4,4'-
diaminodiphenylmethane
1,2-
Benzenedicarboxylic
acid, bis(2-
methoxyethyl
dimethyl sulphate

benzo[a]pyrene
Fatty acids, C16-18,
lead salts
[phthalato(2-)]dioxotrilead
Silicic acid (H2Si2O5),
barium salt (1:1),
lead-
Sulfurous acid, lead
salt, dibasic
Borate(1-),
tetrafluoro-, lead (2+)
dioxobis(stearato)trilead
tetralead trioxide
sulphate
Lead-titanium-trioxide
lead oxide sulfate
Silicic acid, lead salt
lead dinitrate
cadmium
lead
[4-[[4-anilino-1-
naphthyl][4-
(dimethylamino)phen
1,3,5-
tris(oxiranylmethyl)-1,3,5-
triazine-2,4,6(
Lead oxide
trilead bis(carbonate)
dihydroxide
orange lead
cadmium oxide (non-
pyrophoric)
Diboron-trioxide
cadmium carbonate
N,N,N',N'-
tetramethyl-4,4'-
methylenedianiline
2,2'-dichloro-4,4'-
methylenedianiline
dichromium
tris(chromate)

**Halogen-Free
Status**

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[39940](#) Series

Mates With
[395310004](#) , [395311004](#) , [395321004](#) ,
[395320004](#)

This document was generated on 01/04/2021
PLEASE CHECK [WWW.MOLEX.COM](#) FOR LATEST PART INFORMATION