



Part Number : [39000046](#)

Product Description : Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 28-22 AWG, Reel

Series Number : 5556

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 5556T2

Packaging Alternative : [39000047](#) (Bag)



Documents and Resources

Drawings

[039000046 sd.pdf](#)

[55560001-PK-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[55560001-AS-000.pdf](#)

[55560002-AS-000.pdf](#)

[55560002-PS-CH-000.pdf](#)

[55560002-PS-ES-000.pdf](#)

[55560002-PS-SK-000.pdf](#)

[55560008-TS-000.pdf](#)

[PS-5556-001-001.pdf](#)

[PS-5556-002-001.pdf](#)

[55560000-TS-000.pdf](#)

[55560001-TS-000.pdf](#)

[55560010-TS-000.pdf](#)

[TS-5556-002-001.pdf](#)


Tooling Specifications

[CS-5556X2 5558X2-031.pdf](#)

[CS-5556X2 5558X2-032.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5556
Description	Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 28-22 AWG, Reel
Application	Wire-to-Board, Wire-to-Wire
Product Name	Mini-Fit

UPC	800753627710
-----	--------------

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	165.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit Jr. Receptacle Housings	<u>5557</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>44516</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>42474</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>43760</u>
Mini-Fit Jr. Dual Row Receptacle	<u>46992</u>

Housings	
----------	--

Application Tooling

Global

Description	Part Number
Extraction Tool for Mini-Fit Jr. Terminals	<u>11030044</u>
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 28-22 AWG	<u>638191000</u>
FineAdjust Applicator for Insulation Diameter 1.30-1.50mm, 28-22 AWG Wire	<u>639002700</u>
FineAdjust Applicator for Insulation OD 1.10-1.30mm - 28-22 AWG	<u>639020200</u>
FineAdjust Applicator for Insulation OD 0.95-1.08mm - 28-22 AWG	<u>639023800</u>
T2 Terminator for Insulation OD 1.30-1.50mm, 28-22 AWG	<u>639102700</u>
T2 Terminator for insulation OD 1.10-1.30mm - 28-22 AWG	<u>639120200</u>
T2 Terminator for Insulation Diameter 0.95-1.08mm, 28-22 AWG	<u>639123800</u>

Japan

Description	Part Number
S-1 Applicator for Mini-Fit Plug and Receptacle Terminals, 28-22 AWG	<u>570223720</u>
Hand Extraction Tool	<u>570316000</u>