

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1554216001

Status:

Active

Overview:

Flamar Standard and Custom Cables for Industrial Automation

Description:

Flamar Ethernet 5e Network Cable, WSOR Jacket, Braided Shielding Overall, 4 Circuits, 2x(2x0.14mm²) / 2x(2x26 AWG), 6.50mm (.256") Diameter, 300.0m (984.25') Length, Teal

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E172949
General	
Product Family	Cable
Series	155421
Comments	3 reels of 100.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Network
Protocol	EtherNet 5e
Taxonomy	Industrial Cable
UPC	889056464819
Physical	
Bending Radius - Minimum	> 15xOD
Cable Length	300.0m
Circuits (Loaded)	4
Color - Cable Jacket	Teal
Insulation	PE
Material - Outer Jacket	WSOR
Net Weight	0.052/kg
Outer Jacket Diameter	6.50mm
Packaging Type	Reel
Temperature Range - Operating	-10° to +60°C
Wire Size AWG	26
Wire Size mm²	0.14
Wire/Cable Type	UL AWM 21215 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V
Material Info	
Engineering Number	3X100M



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

155421 Series

Use With

Micro-Change (M12) 130047 , 120100 , 130034 , 120071

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION