



Pushing Performance
Since 1945

M12 A-cod 4-pol an/- m/- PUR PP 1.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 40 220 0442 010
Specification	M12 A-cod 4-pol an/- m/- PUR PP 1.0m
HARTING eCatalogue	https://harting.com/21402200442010

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 A-coding Male Angled
Type of cable	Copper cable (round)

Version

Cable length	1 m
Number of cores	4
Core structure	4x 0.34 mm ²
Shielding	Shielded
Number of contacts	4
Coding	A-coding
Locking type	PushPull

Technical characteristics

Rated voltage	48 V AC 60 V DC
Limiting temperature	-50 ... +80 °C moved -30 ... +80 °C unmoved
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.4 mm ± 0.2 mm



Pushing Performance
Since 1945

Technical characteristics

Minimum bending radius	5x Cable diameter (singular bending)
	10x Cable diameter (repeated bending)

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black

Commercial data

Packaging size	1
Net weight	75 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140284906
eCl@ss	27060311 Assembled sensor actuator-line
UNSPSC 24.0	26121604