



Part Number : [2196110150](#)
Product Description : Wi-Fi 6E Low Gain Flex
Antenna, 15.40mm Width, 150.00mm Cable Length,
Compatible with U.FL/ MHF Connectors
Series Number : 219611
Status : Active
Product Category : Antennas

Documents & Resources

Drawings

[2196110150 sd.pdf](#)
[2196110100-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[2196110100-000.pdf](#)
[2196110100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)
• EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	219611
Description	Wi-Fi 6E Low Gain Flex Antenna, 15.40mm Width, 150.00mm Cable Length, Compatible with U.FL/ MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	Wi-Fi 6E Low Gain Flex Antenna
Protocol	BLE, BT, Wi-Fi, Wireless Hart, Zigbee
Type	Internal, Wi-Fi Antenna
UPC	195842855151

Electrical

Band#1 F_End (MHz)	2500
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5850
Band#2 F_Start (MHz)	5150
Band#3 F_End (MHz)	7125
Band#3 F_Start (MHz)	5925
Electrical Connectivity	Cable

Peak Gain (dBi)	2.3 @ 2.4 GHz, 3.1 @ 5 GHz, 3.4 @ 5 GHz
Return Loss - S11 (dB)	< -10
Total Efficiency	>69% @ 5.9 GHz, >70% @ 5 GHz, >72% @2.4 GHz

Physical

Cable Length	150.00mm
Length	35.40mm
Mounting Style	Adhesive
Net Weight	0.778/g
Packaging Type	PET Bag
Polarization	Linear
Radiation Pattern	Omnidirectional
Width	15.40mm