

MICRO SWITCHFREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929**SWITCH—BASIC**

CATALOG LISTING

BZ-2R258

AGR9025

BZ-2R258

PAGE 1 OF 1

MDRAWING
NUMBER

ISSUE

6

REPLACES X70641-BZ

RELEASE NO. PR-8523

CHECK

VISIONS

A CO
58037SMA
1 OCT 85B CO
77591DAW
22 JUN 94

C C093346

DLT
1 SEP 98D CO
94212-CDLT
14 SEP 99

E 0018448

DVM
17 FEB 06

17 FEB 06

RJ

CHECK

8 MAR 80

C E B

8 MAR 80

C E B

CHECK

80


MAR

J A P 16

FORMTEK


FO-52848-A

DRAWN

**NOTE**MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE ——— 9—13 OZ

RELEASE FORCE ——— 4 OZ MIN

DIFFERENTIAL TRAVEL ——.0004—.0020

OVERTRAVEL ——— .005 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D T15A-125, 250 OR 480 VAC, 2A-600 VAC
1/8HP-125 VAC; 1/4HP-250 VAC
CODE L74 1/2A-125 VDC; 1/4A-250 VDCL288
L315
L306

16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/64	X	0.015
ONE PLACE	X,X	0.4/016	X,X	0.38/015
TWO PLACES	X,X,X	0.15/006	X,X,X	0.13/005
THREE PLACES	X,X,X,X		X,X,X,X	
ANGLES				

DESIGN UNITS ☐ SI METRICUS CUSTOMARY ☒

WEIGHT .050 LB