




JKL LAMP NUMBER	VOLTS RATED	AMPS ±10%	MSCP ±25%	LUMENS ±25%	AVERAGE LIFE HRS.	FILAMENT TYPE
11	2.5	.200	.200	2.51	500	C-2R
56	5.0	.115	.150	1.89	40,000	C-2R
79	6.0	.200	.630	7.92	1,000	C-2R
86	6.3	.200	.400	5.03	50,000	C-2F
18	14.0	.040	.130	1.63	5,000	C-2F
73*	14.0	.080	.300	3.77	15,000	C-2F
37	14.0	.090	.500	6.29	2,500	C-2F
74	14.0	.100	.700	8.80	500	C-2F
85	28.0	.040	.300	3.77	25,000	C-2F
17	28.0	.065	.650	8.17	5,000	C-2F

*LAMP LEAD (Pb) FREE

CONTACT JKL FOR LEAD (Pb) FREE LOT IDENTIFICATION.

METRIC			DIMENSIONS ARE IN MILLIMETERS		JKL COMPONENTS CORPORATION				
 THIRD ANGLE PROJECTION			TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		TITLE				
					T-1 3/4 STANDARD GLASS WEDGE BASE				
DRAWN BY			APP'D BY		DATE	SIZE	FSCM NO.	DRAWING NO.	GLASS WEDGE BASE T-1 3/4
L. WENGSTROM			J.K.		2/17/05	A	55335		
- CAD DRAWING -			MANUAL REVISIONS NOT PERMITTED		SCALE	RELEASED DATE	REVISION DATE	REV. NO.	SHEET
					NONE	5/11/00	2/17/05	A	1 OF 1
REV. NO.	DESCRIPTION/ECO NUMBER		APP'D DATE						
A	NOTE #73 TO LEAD (Pb) FREE		2/17/05						
	RELEASED & CANCEL GW-STD-T1 3/4, 75X & 84		5/11/00						