



**Part Number :** [1300090846](#)

**Product Description :** Mini-Change A-Size Double-Ended Cordset, Male 4-Pole (Straight) to Female 5-Pole (Straight), 16 AWG, Yellow TPE Cable, 2.0m (6.56') Length

**Series Number :** 130009

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 130009-0846-M020



---

## Documents and Resources

### Drawings

[1300090846\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3; 10(a) per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	130009
Description	Mini-Change A-Size Double-Ended Cordset, Male 4-Pole (Straight) to Female 5-Pole (Straight), 16 AWG, Yellow TPE Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Double Ended
UPC	78172551792

### Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	600V

### Physical

Cable Diameter	10.92mm (.430")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single

LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	199.000/g
Orientation	Straight to Straight
Poles	4, 5
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	TC-ER
Wire Size (AWG)	16

---

This document was generated on Jun 10, 2026