


REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVLED/DATE
A	/	NEW RELEASE	May 2017-07-04	Rain 2017-07-04	Leo 2017-07-04
B	/	Update the drawing frame	May 2019-11-28	Rain 2019-11-28	Leo 2019-11-28


NO.	COMPONENTS	MATERIALS	FINISH/COLOR SPECIFICATION	QTY
1	HOUSING	LCP,UL94V-0	Natural or Black	1
2	ACTUATOR	PA9T,UL94V-0	Black	1
3	TERMINAL	PHOSPHOR BRONZE T=0.15mm	UNDER PLATING:1~3μm Ni SURFACE PLATING:0.05μm Min. Au	N
4	STATOR	BRASS,C2680-H T=0.20mm	UNDER PLATING:1~3μm Ni SURFACE PLATING:2~5μm Sn	2
5	MYLAR	T=0.10mm THERMOSTABLE	yellow	1






NOTE:
1.ALL MATERIAL MUST BE COMPLY WITH GGP-001/OR/RoHS.
2.PART NO. LEGEND:
F305-1*7H1-110**-E*00
1A:Natural
1B:Black
1: WITH MYLAR
2. WITHOUT MYLAR
NO. OF POSITIONS






APPLICABLE FPC/FFC



3d view ref.

DIMENSION LIST:

PIN No.of	A	B	C	E
10	9.30	4.50	5.50	7.25
20	14.30	9.50	10.50	12.25
30	19.30	14.50	15.50	17.25
36	22.30	17.50	18.50	20.25
40	24.30	19.50	20.50	22.25
45	26.80	22.00	23.00	24.75
50	29.30	24.50	25.50	27.25
60	34.30	29.50	30.50	32.25



RECOMMEND PCB LAYOUT;TOL:±0.05

UNLESS OTHERWISE SPECIFIED TOLERANCES

X.	±0.30	X. °	± 5°
X.X	±0.25	X.X °	± 4°
X.XX	±0.20	X.XX °	± 3°
X.XXX	±0.15	X.XXX °	± 2°
LINEAR DIMS		ANGLES DIMS	

ANGLE OF PROJECTION

DWG NO.:	A-S0456	
MATERIAL	SEE NOTES	
FINISHED	SEE NOTES	
DOC TYP	Customer Drw	
DRAWN DATE	May	2019-11-28
DESIGN DATE	May	2019-11-28
CHECKED DATE	Rain	2019-11-28
APPROVED DATE	Leo	2019-11-28

Amphenol AORORA
Amphenol Aorora Technology (Huizhou) Co.,Ltd

TITLE:
FFC/FPC P0.50 H2.0 front side filp_"L" type fixed plate


SIZE	PART NUMBER:	REV.
A4	F305-1*7H1-110**-E*00	B

SCALE 5:1 | UNIT : mm | SHEET 1 OF 2

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of AAOR. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of AAOR. © 2019 AAOR

Downloaded from Arrow.com.


1. PACKING INTO REEL:



NOTES:

1. MATERIAL:
   - 1.1 CARRY TAPE:HIPS,T=0.35±0.05mm,CLEAR
   - 1.2 REEL:HIPS,
   - 1.3 SHIM:PE,CLEAR.
2. PRIMARY PACKING:2000PCS/REEL.
3. SECONDARY PACKING:SEE PACKING LIST
4. PEELING RESISTANCE: 0.1~0.7N(10~70gf); PEELING ANGLE: 165°~180°; PEELING SPEED: 300mm/minutes.

2:PACKING INTO OUTER BOX



5. QTY. LIST:

NO. OF POS.	A	B	PCS/Reel	N Reel/Carton (TOL:PCS)
10~20 PIN	24.0	20.4	2000	11Reel(22000PCS)
21~34 PIN	32.0	28.4	2000	8Reel(16000PCS)
35~54 PIN	44.0	40.4	2000	6Reel(12000PCS)
55~60 PIN	56.0	52.4	2000	5Reel(10000PCS)

UNLESS OTHERWISE SPECIFIED TOLERANCES			
X.	±0.30	X. °	± 5°
X.X	±0.25	X.X °	± 4°
X.XX	±0.20	X.XX °	± 3°
X.XXX	±0.15	X.XXX °	± 2°
LINEAR DIMS		ANGLES DIMS	

ANGLE OF PROJECTION

Amphenol AORORA

Amphenol Aorora Technology (Huizhou) Co.,Ltd

DWG NO.:	A-S0456	DOC TYP	Customer Drw
MATERIAL	SEE NOTES	DRAWN DATE	May 2019-11-28
FINISHED	SEE NOTES	DESIGN DATE	May 2019-11-28
		CHECKED DATE	Rain 2019-11-28
		APPROVED DATE	Hongkui.Liu 2019-11-28

TITLE: FFC/FPC P0.50 H2.0 front side filp_"L" type fixed plate

SIZE	PART NUMBER:	REV.
A4	F305-1*7H1-110**-E*00	B

SCALE	1:1	UNIT : mm	SHEET 2 OF 2

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of AAOR. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of AAOR. © 2019 AAOR

Downloaded from Arrow.com.