
SPECIFICATION CONTROL DRAWING

55AC1833

TITLE: THREE CONDUCTOR CABLE, SHIELDED, JACKETED, GENERAL PURPOSE, 600 VOLT

Date: 2-6-13 | Revision: A

This specification sheet forms a part of the latest issue of Raychem Specification 55A.



CABLE CONSTRUCTION DETAILS							
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inches)		OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT (lbs/1000 ft.)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55AC1833-26-*	26	38	.006	.008	.119	.125	12.6
55AC1833-24-*	24	38	.006	.008	.130	.137	15.2
55AC1833-22-*	22	38	.006	.008	.141	.150	18.9
55AC1833-20-*	20	38	.006	.008	.158	.167	25.0
55AC1833-18-*	18	38	.006	.008	.184	.193	34.3
55AC1833-16-*	16	38	.006	.008	.199	.212	41.5
55AC1833-14-*	14	38	.007	.009	.238	.252	60.6
55AC1833-12-*	12	38	.007	.009	.275	.291	85.0
55AC1833-10-*	10	38	.008	.010	.326	.348	126.
55AC1833-8-*	8	36	.009	.011	.464	.487	238.
55AC1833-6-*	6	34	.010	.012	.571	.602	359.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C
Maximum continuous conductor temperature
VOLTAGE RATING: 600 volts (rms) at sea level
ACCELERATED AGING: 300 ± 3°C for 7 hours
BLOCKING: 200 ± 3°C for 6 hours
DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz
FLAMMABILITY (Procedure 1): 3 seconds (maximum); 3 in. (maximum); no flaming of facial tissue
JACKET COLOR: White preferred
JACKET ELONGATION AND TENSILE STRENGTH:
Elongation, 50% (minimum)
Tensile Strength, 5000 lbf/in² (minimum)
JACKET FLAWS:
Spark Test, 1000 volts (rms)
Impulse Dielectric Test, 6.0 kV (peak)

NOTE: Nominal values are for information only.
Nominal values are not requirements.

LIFE CYCLE: 230 ± 3°C for 500 hours
LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours
SHIELD COVERAGE: 90% (minimum)
VOLTAGE WITHSTAND (Post Environmental):
1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:
The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.

1/ Example: AWG 20, black, brown and red component wires; white jacket: 55AC1833-20-0/1/2-9

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Raychem, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

Raychem Wire & Cable
501 Oakside Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297

© 2013 Tyco Electronics Corporation. All rights reserved.

Downloaded from Arrow.com.