

SuperChassis 732D4-903B

Products ▶ Chassis ▶ Mid-tower ▶ [SC732D4-903B]



Key Features

- 4x 3.5" internal SAS/SATA HDD Bays
90° rotatable HDD cage design
4x 2.5" internal SAS/SATA HDD (opt.)
- Peripheral Drive Bays:
2x 5.25" and 1x 3.5"
- 1x 12cm Rear Exhaust Fan
1x 12cm Front Cooling Fan (opt.)
- 7x Full-height, Full-length PCI Expansion Slots
- Front I/O ports: 2x Audio (HD/AC97),
2x USB 3.0, 2x USB 2.0 ports
- 900W High Efficiency Power Supply
Gold Level Certified
- Cost Effective Desktop, Embedded,
Workstation Chassis

Available Colors

Black



Downloads

Chassis
Manual



Note: Image above may show a varied configuration or optional parts, Please refer to parts list for standard parts included.

Specifications

Product SKU	
CSE-732D4-903B	SuperChassis 732D4-903B (Black)
Form Factor	
Mid-Tow er chassis support for motherboard sizes - 12" x 13" E-ATX, 12" x 10" ATX, and 9.6" x 9.6" Micro-ATX	
Processor Support	
Supports dual, single Intel® / AMD processors	
Dimensions	
Width	7.6" (193 mm)
Height	16.7" (424 mm)
Depth	20.68" (525.3 mm)
Packaging	21.38" (W) x 11.97" (H) x 25.28" (D) 543mm (W) x 304mm (H) x 642mm (D)
Weight	30 lbs (13.6 kg)
Available Colors	Black
Expansion Slots	
7x Full-height, Full-length I/O expansion slots	
Drive Bays	
Internal	4x 3.5" SAS/SATA HDD Bays (90° rotatable drive cage) SAS or enterprise SATA HDD only recommended
Peripheral Bay	2x 5.25" peripheral drive bays 1x 3.5" peripheral drive bay
Front Panel	
Buttons	Pow er On/Off button
LEDs	Pow er status LED Hard drive activity LED Netw ork activity LED System Overheat LED
Ports	2x Front USB 3.0 ports 2x Front USB 2.0 ports 2x Front HD/AC97 Audio ports

Servers (for SC732D4-903B)	
5037A-I, 7038A-I, 5038A-I	
System Cooling	
Fans	1x 12cm (1850rpm) rear exhaust fan 1x 12cm (1850rpm) front cooling fan (opt.) Optimized Cooling Technology at 21dB Whisper-Quiet Operation
Operating Environment (System)	
Operating Temperature Range	5°C ~ 35°C (41°F ~ 95°F)
Non-Operating Temperature Range	-40°C ~ 60°C (-40°F ~ 140°F)
Operating Relative Humidity Range	8% ~ 90% (non-condensing)
Non-Operating Relative Humidity Range	5% - 95% (non-condensing)
Power Supply	
900W AC multi output pow er supply	
AC Voltage	100-240 V, 50-60 Hz, 10-6 Amp
+5V Standby	3 Amp
+12V1	25 Amp
+12V2	25 Amp
+12V3	25 Amp
+12V4	25 Amp
+5V	25 Amp
+3.3V	25 Amp
-12V	0.5 Amp
Certification	Gold Level
Note:	• Max. continuous combined load on +3.3V and +5V output shall not exceed 155W. • Max. continuous combined load on +12V1, +12V2, +12V3 and +12V4 output shall not exceed 860W.
Regulatory (Power Supply)	
Power Supply Safety / EMC	USA - UL listed, FCC Canada - CUL listed Germany - TUV Certified Europe/CE Mark EN 60950/IEC 60950-Compliant CCC Certified

Components

[See Parts List](#)