MJE4343 (NPN), MJE4353 (PNP)

High-Voltage - High Power Transistors

. . . designed for use in high power audio amplifier applications and high voltage switching regulator circuits.

Features

- High Collector−Emitter Sustaining Voltage −
  NPN PNP
  $V_{CEO(sus)}$ = 160 Vdc − MJE4343 MJE4353
- High DC Current Gain − @ I_C = 8.0 Adc h_{FE} = 35 (Typ)
- Low Collector−Emitter Saturation Voltage −
  $V_{CE(sat)}$ = 2.0 Vdc (Max) @ I_C
  = 8.0 Adc
- These are Pb−Free Devices

MAXIMUM RATINGS

Rating	Symbol	Max	Unit
Collector−Emitter Voltage	V_{CEO}	160	Vdc
Collector−Base Voltage	V_{CB}	160	Vdc
Emitter−Base Voltage	V_{EB}	7.0	Vdc
Collector Current − Continuous Peak (Note 1)	I_C	16 20	Adc
Base Current − Continuous	I_B	5.0	Adc
Total Power Dissipation @ T_C = 25°C	P_D	125	Watts
Operating and Storage Junction Temperature Range	T_J, T_{stg}	−65 to +150	°C

THERMAL CHARACTERISTICS


Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction to Case	$R_{\theta JC}$	1.0	°C/W

1. Pulse Test: Pulse Width ≤ 5.0 μs, Duty Cycle ≥ 10%.


ON Semiconductor®

http://onsemi.com

16 AMPS
POWER TRANSISTORS
COMPLEMENTARY
SILICON
160 VOLTS



SOT−93
CASE 340D
STYLE 1



TO−247
CASE 340L
STYLE 3

NOTE: Effective June 2012 this device will be available only in the TO−247 package. Reference FPCN# 16827.


ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

© Semiconductor Components Industries, LLC, 2012

Downloaded from Arrow.com.

MARKING DIAGRAMS



MJE43x3	= Device Code
A	= Assembly Location
Y	= Year
WW	= Work Week
G	= Pb−Free Package

ORDERING INFORMATION

Device Order Number	Package Type	Shipping
MJE4343G	SOT−93 (Pb−Free)	30 Units / Rail
MJE4353G	SOT−93 (Pb−Free)	30 Units / Rail
MJE4343G	TO−247 (Pb−Free)	30 Units / Rail
MJE4353G	TO−247 (Pb−Free)	30 Units / Rail




Figure 1. Power Derating
Reference: Ambient Temperature


Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
OFF CHARACTERISTICS				
Collector−Emitter Sustaining Voltage (Note 2) (I_C = 200 mAdc, I_B = 0)	$V_{CEO(sus)}$	160	–	Vdc
Collector−Emitter Cutoff Current (V_{CE} = 80 Vdc, I_B = 0)	I_{CEO}	–	750	μAdc
Collector−Emitter Cutoff Current (V_{CE} = Rated V_{CB}, $V_{EB(off)}$ = 1.5 Vdc) (V_{CE} = Rated V_{CB}, $V_{EB(off)}$ = 1.5 Vdc, T_C = 150°C)	I_{CEX}	– –	1.0 5.0	mAdc
Collector−Base Cutoff Current (V_{CB} = Rated V_{CB}, I_E = 0)	I_{CBO}	–	750	μAdc
Emitter−Base Cutoff Current (V_{BE} = 7.0 Vdc, I_C = 0)	I_{EBO}	–	1.0	mAdc
ON CHARACTERISTICS (Note 2)				
DC Current Gain (I_C = 8.0 Adc, V_{CE} = 2.0 Vdc) (I_C = 16 Adc, V_{CE} = 4.0 Vdc)	h_{FE}	15 8.0	35 (Typ) 15 (Typ)	–
Collector−Emitter Saturation Voltage (I_C = 8.0 Adc, I_B = 800 mA) (I_C = 16 Adc, I_B = 2.0 Adc)	$V_{CE(sat)}$	– –	2.0 3.5	Vdc
Base−Emitter Saturation Voltage (I_C = 16 Adc, I_B = 2.0 Adc)	$V_{BE(sat)}$	–	3.9	Vdc
Base−Emitter On Voltage (I_C = 16 Adc, V_{CE} = 4.0 Vdc)	$V_{BE(on)}$	–	3.9	Vdc
DYNAMIC CHARACTERISTICS				
Current−Gain − Bandwidth Product (Note 3) (I_C = 1.0 Adc, V_{CE} = 20 Vdc, f_{test} = 0.5 MHz)	f_T	1.0	–	MHz
Output Capacitance (V_{CB} = 10 Vdc, I_E = 0, f = 0.1 MHz)	C_{ob}	–	800	pF

2. Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≥ 2.0%.
3. $f_T = |h_{fe}| \bullet f_{test}$.

Downloaded from Arrow.com.



R_B and R_C VARIED TO OBTAIN DESIRED CURRENT LEVELS
D_1 MUST BE FAST RECOVERY TYPE, e.g.:
1N5825 USED ABOVE $I_B \approx$ 100 mA
MSD6100 USED BELOW $I_B \approx$ 100 mA

Note: Reverse polarities to test PNP devices.

Figure 2. Switching Times Test Circuit




Figure 3. Typical Turn−On Time

TYPICAL CHARACTERISTICS




Figure 4. Turn−Off Time




Figure 5. On Voltages

Downloaded from Arrow.com.

DC CURRENT GAIN




Figure 6. MJE4340 Series (NPN)




Figure 7. MJE4350 Series (PNP)




Figure 8. Collector Saturation Region




Figure 9. Thermal Response

Downloaded from Arrow.com.




Figure 10. Maximum Forward Bias Safe Operating Area

REVERSE BIAS

For inductive loads, high voltage and high current must be sustained simultaneously during turn−off, in most cases, with the base to emitter junction reverse biased. Under these conditions the collector voltage must be held to a safe level at or below a specific value of collector current. This can be accomplished by several means such as active clamping, RC snubbing, load line shaping, etc. The safe level for these devices is specified as Reverse Bias Safe Operating Area and represents the voltage−current conditions during reverse biased turn−off. This rating is verified under clamped conditions so that the device is never subjected to an avalanche mode. Figure 11 gives RBSOA characteristics.

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate $I_C - V_{CE}$ limits of the transistor that must be observed for reliable operation; i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 10 is based on T_C = 25°C; $T_{J(pk)}$ is variable depending on power level. Second breakdown pulse limits are valid for duty cycles to 10% but must be derated when $T_C \geq 25°C$. Second breakdown limitations do not derate the same as thermal limitations. Allowable current at the voltages shown on Figure 10 may be found at any case temperature by using the appropriate curve on Figure 9.




Figure 11. Maximum Reverse Bias Safe Operating Area


Downloaded from Arrow.com.

MECHANICAL CASE OUTLINE
PACKAGE DIMENSIONS


ON Semiconductor®

SOT−93 (TO−218)
CASE 340D−02
ISSUE E

DATE 01/03/2002



SCALE 1:1




STYLE 1:
PIN 1. BASE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 2:
PIN 1. ANODE
2. CATHODE
3. ANODE
4. CATHODE

NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.

	MILLIMETERS		INCHES	
DIM	MIN	MAX	MIN	MAX
A	---	20.35	---	0.801
B	14.70	15.20	0.579	0.598
C	4.70	4.90	0.185	0.193
D	1.10	1.30	0.043	0.051
E	1.17	1.37	0.046	0.054
G	5.40	5.55	0.213	0.219
H	2.00	3.00	0.079	0.118
J	0.50	0.78	0.020	0.031
K	31.00 REF		1.220 REF	
L	---	16.20	---	0.638
Q	4.00	4.10	0.158	0.161
S	17.80	18.20	0.701	0.717
U	4.00 REF		0.157 REF	
V	1.75 REF		0.069	

MARKING DIAGRAM



A = Assembly Location
Y = Year
WW = Work Week
xxxxx = Device Code

DOCUMENT NUMBER:	**98ASB42643B**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	**SOT−93**		**PAGE 1 OF 1**

ON Semiconductor and ON are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.


© Semiconductor Components Industries, LLC, 2019

Downloaded from Arrow.com.


MECHANICAL CASE OUTLINE
PACKAGE DIMENSIONS

TO−247
CASE 340L
ISSUE G

DATE 06 OCT 2021




SCALE 1:1



NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER

	MILLIMETERS		INCHES	
DIM	MIN.	MAX.	MIN.	MAX.
A	20.32	21.08	0.800	0.830
B	15.75	16.26	0.620	0.640
C	4.70	5.30	0.185	0.209
D	1.00	1.40	0.040	0.055
E	1.90	2.60	0.075	0.102
F	1.65	2.13	0.065	0.084
G	5.45 BSC		0.215 BSC	
H	1.50	2.49	0.059	0.098
J	0.40	0.80	0.016	0.031
K	19.81	20.83	0.780	0.820
L	5.40	6.20	0.212	0.244
N	4.32	5.49	0.170	0.216
P	----	4.50	----	0.177
Q	3.55	3.65	0.140	0.144
U	6.15 BSC		0.242 BSC	
W	2.87	3.12	0.113	0.123

GENERIC MARKING DIAGRAM*



XXXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
G = Pb−Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

STYLE 1:
PIN 1. GATE
2. DRAIN
3. SOURCE
4. DRAIN

STYLE 2:
PIN 1. ANODE
2. CATHODE (S)
3. ANODE 2
4. CATHODES (S)

STYLE 3:
PIN 1. BASE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 4:
PIN 1. GATE
2. COLLECTOR
3. EMITTER
4. COLLECTOR

STYLE 5:
PIN 1. CATHODE
2. ANODE
3. GATE
4. ANODE

STYLE 6:
PIN 1. MAIN TERMINAL 1
2. MAIN TERMINAL 2
3. GATE
4. MAIN TERMINAL 2

DOCUMENT NUMBER:	**98ASB15080C**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**TO−247**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT
North American Technical Support:
Voice Mail: 1 800−282−9855 Toll Free USA/Canada
Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:
Phone: 00421 33 790 2910
For additional information, please contact your local Sales Representative

◊

Downloaded from Arrow.com.