

COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 1.0 GHz

3401.01.C

Properties

- Broadband frequency operation from DC to 1 GHz
- Gas discharge tube replaceable and not included
- DC/AC remote powering via coaxial same cable
- Surge current handling capability 30 kA once and 20 kA multiple
- Semper self-extinguishing functionality optional



Product configuration

Main path connectors	Port 1: unprotected, BNC plug (male) Port 2: protected, BNC jack (female)
Mounting and grounding	MH12 (bulkhead mounting)
Side of bulkhead	protected side
EMP can be install reversed	YES

Interface and material data

Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Brass / Gold Plating (without Nickel underplating) Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)

Electrical data

Impedance	50 Ω
Frequency frame	0 MHz to 1000 MHz
Return loss typical	19 dB
Insertion loss typical	0.1 dB
CW power frame	150 W
Residual pulse energy (typ.)	350 μJ (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
Residual pulse voltage (typ.)	650 V (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
Surge current handling capability	30 kA single, 20 kA multiple (test pulse 8/20 μs)

Electrical bands

	Range 1
Frequency range	0 MHz ... 300 MHz

COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 1.0 GHz

3401.01.C

Electrical bands

	Range 1
Return loss typical	26.44 dB
Insertion loss	0.1 dB
Power avg. / peak	150 W / -
PIM 3rd order	0 dBc

Electrical remarks

Gas tube	Yes DC, GDT not included
Electrical remarks	Data refer to GDT 9071.99.0547, 230 V

Mechanical data

Weight	90 g
Mating cycles	500

Environmental data

Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	IP20
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. D
Moisture resistance according	MIL-STD-202, Method 106

Compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
22646113	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table

Item number	Item description
22646113	3401.01.C

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2039 / Date of publication: 28.02.2025 / uncontrolled copy