

## Technical data sheet

Article number:  
170-10800

HEGP08



<b>Product Group</b>	Standard polyester braided sleeving
<b>Product Family</b>	Helagaine HEGP
<b>Material</b>	Polyester (PET)
<b>Colour</b>	Black (BK)
<b>Application Method</b>	To prevent fraying, the sleeve can be cut with the hot cutting tool HSG0, see page
<b>Bundle Ø max.</b>	12 mm
<b>Bundle Ø min.</b>	5 mm
<b>Melting Point</b>	+250 °C
<b>Operating Temperature</b>	-50 °C to +150 °C
<b>Package Content packed in</b>	metre
<b>Pack Cont.</b>	100 m
<b>Specifications</b>	ECE R-118-03 Abschnitt 6 / Annex 6, ECE R-118-03 Abschnitt 8 / Annex 8, EN 45545-2

HF ✓ RoHS ✓

**EN 45545-2** **ECE R-118**