



Description

- PLL based, one time only factory programmable (for a fast lead time) crystal oscillator in a hermetically sealed 8-pin DIL metal package.
This model is not approved for on-board avionics applications; in such instances our 'CFPP-23 AVIATION' version should be specified.
- Model CFPP-23
- Model Issue number 11

Frequency Parameters

- Frequency 32.0MHz
- Frequency Stability $\pm 50.00\text{ppm}$
- Operating Temperature Range -40.00 to 85.00°C
- Ageing $\pm 5\text{ppm}$ max in 1st year @ 25°C

Electrical Parameters

- Supply Voltage $5.0\text{V} \pm 0.5\text{V}$
- Current Draw 45.00mA

Output Details

- Output Compatibility CMOS
- Drive Capability 50pF
- Rise and Fall Time 4.0ns max
- Duty Cycle $45/55\%$
- Logic '1' to pin 1 enables oscillator output
Logic '0' to pin 1 disables oscillator output; when disabled the oscillator output goes to the high impedance state
No connection to pin 1 enables oscillator output

Noise Parameters

- Jitter pk-pk (typical)
1 to 33MHz $>33\text{MHz}$
100ps 75ps
- Jitter pk-pk (max)
1 to 33MHz $>33\text{MHz}$
250ps 175ps

Environmental Parameters

- Storage Temperature Range: -55 to 125°C

Compliance


- RoHS Status (2011/65/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details


- Pack Style: Bulk Loose in bulk pack
Pack Size: 1
- Alternative packing option available



Outline (mm)



Test Circuit





Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: 0800 1808 443

France: 0800 901 383
USA: +1.760.318.2824

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com

Test Circuit

Wave Form

Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: 0800 1808 443

France: 0800 901 383
USA: +1.760.318.2824

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com