










CAPPED VIEW



REAR VIEW



RECOMMEND MINIMUM MOUNTING PITCH



RECOMMEND PANEL CUT OUT

PART NUMBER	CONTACT FINISH
AXS5MP1	TIN PLATED
AXS5MP1-AU	GOLD PLATED

NOTE:
1. MATING CONNECTOR SHELL TO HAVE MIN 1.6 SURFACE FINISH TO ACHIEVE IP RATING OF THIS CONNECTOR.
2. BLACK MOUNTING SCREW 52500011-430 x 4 PCS TO BE SUPPLIED WITH THE CONNECTOR, MAX TORQUE 0.5Nm.
3. DUE TO 0.4mm THICK RUBBER SEAL, THE DIM WILL VARY DEPENDING ON THE SCREWS TIGHTENING IN ASSEMBLY.

3	52730035-000	AXS FRONT FLANGE D TYPE RUBBER SEAL IP54 WITH CAP	1
2	52500011-430	SCREW 2.9 x 1.06mm USED FOR PLASTIC MATERIAL	4
1	55011499-005/905	AXS5MP WITHOUT RUBBER FLANGE - TIN/GOLD PLATED CONTACT	1
ITEM	PART NUMBER	DESCRIPTION	QTY

UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE	
LINEAR	ANGULAR
X ± 0.5	X' ± 1
X.X ± 0.2	X.X' ± 30'
X.XX ± 0.1	X.XX' ± 15'
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS	
DO NOT SCALE	
DIMENSIONS IN MILLIMETRES	

THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD.
NO PART THEREOF MAY BE REPRODUCED AND USED
WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER

MATERIAL:
SEE COMPONENT

FINISH:
SEE COMPONENT



THIRD ANGLE
PROJECTION

DRN: M.H	DATE: 11-11-23
CKD: M.H	DATE: 11-11-23
APP'D: P.M	DATE: 11-11-23
SCALE: 1:1	SIZE: A4

Amphenol Amphenol Australia Pty.Ltd,
22 Industry Blvd, Carrum Downs, VIC 3201

TITLE:
**AXS5MP1
AXS PANEL MOUNT SERIES
CUSTOMER DRAWING**

CAD FILE: 55011499815110

PART No. SEE TABLE	
DRAWING No. 55011499-815-2	SHEET 2/2