




0697-0-15-XX-30-XX-10-0



General Info

Description¹: Press-Fit Receptacle for Non-Plated Through Hole

Mounting Feature: Press-Fit into a Non-Plated Through Hole (NPTH)

Mounting Hole²: .057" (1,448mm)

Pin Diameter .015"-.025" (0,381-0,635mm)

Packaging: Packaged in Bulk

RoHS³: Yes

Product Lifecycle⁴: Active

Country Of Origin: USA

Materials

Shell Material ⁵: Brass Alloy

Shell Plating⁶: 10 μ" Gold over Nickel

Contact Plating⁷: 30 μ" Gold over Nickel

Technical Specs

Mechanical life (Durability)⁸: 1,000 Cycles Minimum

Operating Temperature Range⁹: -55/+125° C

Maximum Current: 12A @ 30° C Temp. Rise

**Maximum
Derated
Current:** 9.6A

Contact Resistance: 10 mΩ Max


Shock ¹⁰ :	No Elect. Discontinuity > 1μs @ 50g
-----------------------	--

Vibration¹¹:	No Elect. Discontinuity > 1μs @ 10-2000HZ, 20 G
--------------------------------	--

NOTES:

- 1. Standard Tolerances:
Lengths +/- .005" (0,13)
Diameters: +/- .002" (0,051)
Angles: +/- 2°
- 2. This is a general guideline; your application may require different specifications
- 3. Mill-Max products labeled with the RoHS symbol are compliant with all three ROHS Directives. All of our products previously described as RoHS (2002/95/EC) and RoHS-2 (2011/65/EC) are also compliant with RoHS-3 (2015/863/EU).
- 4. Part is Active and in Production, No Scheduled Obsolescence
- 5. Brass Alloy 360 per ASTM B 16, or 385 per ASTM B455
- 6. GOLD per ASTM B 488, Type 1 (99.7% min. gold), Code C (130-200 HK {Knoop hardness}); NICKEL per ASTM B 689, Type 2 (Bright),
- 7. GOLD per ASTM B 488, Type 1 (99.7% min. gold), Code C (130-200 HK {Knoop hardness}), NICKEL per ASTM B 689, Type 2 (Bright)
- 8. Receptacles are capable of 1,000 Minimum insertion/extraction cycles for a broad range of applications. Mating pin size, shape and finish, along with application specific variables, will affect the life of a receptacle contact.
- 9. Per IEC 60512-11-(4,-9,-10,-12)
- 10. Per IEC 60512-6-3: Test 6c: Shock
- 11. Per IEC 60512-6-4: Test 6d: Vibration (sinusoidal)

CONTACT:



Material	Beryllium Copper	Fingers	4
Compliancy (δ)	0.005	Length	.083" (2,108mm)
Maximum Current	12A @ 30° C Temp. Rise	Maximum Operating Temp @ Max Current	120.00° C
20% De-rated Maximum Current	9.60A	Contact Resistance	10.00mΩ Max
Contact Group	C		

ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance , Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

RELATED LINKS AND DOCUMENTS

Engineering Notebook: (<https://www.mill-max.com/engineering-notebooks/printed-circuit-board-terminal-pins/mill-max-press-fit-pins>)

Environmental Compliance: (<https://www.mill-max.com/rohs>)