



RELAYS, CONTACTORS & SWITCHES

1/5-SIZE RELAYS



✓ Active

TE CONNECTIVITY (TE)

3SBH1147A2=M39016/14-007L

[CII | 3SBH 1/5-Size Relay](#)

3SBH1147A2

TE Internal Number: 1617354-7

Mil-Spec: M39016/14-007L

Not EU RoHS Compliant

Not EU ELV Compliant

Contact Arrangement 4 Form C, 4PDT, 4 C/O

Input Voltage (VDC) 12

Coil Suppression Diode Without

Contact Current Rating (A) 2

Coil Voltage Rating (VDC) 12

[3D PDF](#)

DOCUMENTATION

CAD Files

[**3D PDF**](#)

[PDF](#)

[3D](#)

[**Customer View Model**](#)

[2D_DXF.ZIP](#)

[English](#)

[**Customer View Model**](#)

[3D_IGS.ZIP](#)

[English](#)

[**Customer View Model**](#)

[3D_STP.ZIP](#)

[English](#)

5-1773450-5_sec1_3SBH

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

MOSFET Driver Without

Product Type Relay

Coil Latching Without

Relay Type Military/Aerospace High Performance

Enclosure Type Hermetically Sealed

Configuration Features

Transistor Driver Without

Electrical Characteristics

Coil Polarity Protection Diode Without

Coil Power Measurement Milliwatts

Input Voltage (VDC) 12

Coil Suppression Diode Without

Coil Voltage Rating (VDC) 12

Coil Resistance (Ω) 115

Coil Power Rating (DC) (mW) 1252

Shock 75G's, 6ms

Coil Magnetic System Non-Polarized, Monostable

Vibration 30G's, 10 – 3000Hz

Actuating System DC

Contact Features

Contact Arrangement 4 Form C, 4PDT, 4 C/O

Contact Current Rating (A) 2

Termination Features

Termination Type PC Pins

Mechanical Attachment

Mounting Type Printed Circuit Board

Usage Conditions

Operating Temperature Range (°C) -65 – 125

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
