


Communications/Signal PC Board Relays



✓ Active

 [Add to Part List](#)

Product Highlights:

- V23005/Cradle Relay W Series
- AC Actuating System
- Input Voltage = 110 VAC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 5 Amps.

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

Product Drawings:

- None Available

- None Available

- [Cradle W Relay Datasheet](#) (PDF, English)

- None Available

- None Available

- None Available

- Product Line Information

- Tooling

List all Documents

Product Type Features:

- Termination Type = Solder/Plug-In Terminals

- Actuating System = AC
- Input Voltage (VAC) = 110
- Contact Current Rating (Amps.) = 5
- Coil Resistance (Ω) = 3200
- Coil Power, Nominal (VA) = 0.70 - 1.15
- Dielectric Between Coil and Contacts (V rms) = 2000

- Series = V23005/Cradle Relay W
- Polarized = No

- Mounting Options = Socket
- Enclosure = Dust Protected
- [FCC Part 68 Isolation](#) = No
- Approved Standards = None
- Contact Material = Silver, Gold Overlay
- Approx. Dimensions (L x W x H) (mm [in]) = 30.00 x 19.00 x 40.00 [1.181 x .748 x 1.575]
- Compatible Socket = With
- Contact Type = Single
- Pin Configuration = Industry Standard

- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Coil Magnetic System = Non Polarized, Monostable
- Coil Suppression Diode = Without

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

- Brand = Axicom