

M12-L female crimp B-coded 5pole



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 841 2535
Specification	M12-L female crimp B-coded 5pole
HARTING eCatalogue	https://harting.com/21038412535

Identification

Category	Connectors
Series	Circular connectors M12
Identification	INOX
Element	Cable connector
Specification	Straight

Version

Termination method	Crimp termination
Gender	Female
Shielding	Shielded
Number of contacts	5
Coding	B-coding
Locking type	Screw locking
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 0.75 mm ²
Conductor cross-section [AWG]	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	60 V
Rated impulse voltage	1.5 kV
Pollution degree	3



Pushing Performance
Since 1945

Technical characteristics

Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	17
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Cable diameter	4.5 ... 8.8 mm
Isolation group	I ($600 \leq \text{CTI}$)

Material properties

Material (insert)	Polyamide (PA)
Material (hood/housing)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 61076-2-101
----------------	-----------------

Commercial data

Packaging size	1
Net weight	58.4 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140227453
eCl@ss	27440116 Circular connector (for field assembly)



Pushing Performance
Since 1945

Commercial data

ETIM	EC002635
UNSPSC 24.0	39121413