

4-Channel Vibration Meter/Datalogger



Features:

- Selectable data sampling rate: 1, 2, 5, 10, 30, 60, 120, 300, 600, 1800, 3600 seconds
- Remote vibration sensor with magnetic adapter on 39"(1m) cable
- Wide frequency range of 10Hz to 1kHz
- Basic accuracy of $\pm(5\% + 2$ digits)
- RMS or Peak Value measurement modes
- Datalogger date/time stamps and stores readings on an SD card in Excel® format for easy transfer to a PC
- Data Hold freezes the reading in the display
- Auto Power off saves battery life
- Meets ISO2954 standard
- Complete with 4 remote sensors, magnetic mounts, 8 x AA batteries, 100-240V Universal AC Adaptor, SD card, and heavy duty carrying case

Applications:

- Motors, bearings
- Fans
- Pumps
- Rotating machinery
- Plant maintenance



Specifications	
Acceleration	656ft/s ² , 200m/s ² , 20.39g (peak)
Velocity	7.87in/s, 200mm/s, 19.99cm/s (peak)
Displacement	0.078in, 2mm (peak-to-peak)
Resolution	1ft/s ² , 0.1m/s ² , 0.01g; 0.01in/s, 0.1mm/s, 0.01cm/s; 0.001in, 0.001mm
Basic accuracy	$\pm(5\% + 2$ digits)
Memory	20M data records using 2G SD card
Dimensions	8 x 3 x 1.5" (203 x 76 x 38mm)
Weight	1.13lbs (515g)

Ordering Information (Available Q4, 2011):

VB5004-Channel Vibration Meter/Datalogger
 VB500-NISTVB500 with Certificate Traceable to NIST

