



**Part Number :** [430251600](#)

**Product Description :** Micro-Fit 3.0 Receptacle Housing, Dual Row, 16 Circuits, UL 94V-0, Black

**Series Number :** 43025

**Status :** Active

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[430251600\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[430250000-AS-000.pdf](#)

[430450001-AS-000.pdf](#)

[PK-43025-001-001.pdf](#)

[430450001-PS-KO-000.pdf](#)

[430450001-PS-SP-000.pdf](#)

[PS-43045-001.pdf](#)

[430450005-TS-000.pdf](#)

[430450007-TS-000.pdf](#)


[TS-43045-001-001.pdf](#)

[TS-46235-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC

Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	43025
Description	Micro-Fit 3.0 Receptacle Housing, Dual Row, 16 Circuits, UL 94V-0, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Micro-Fit 3.0
UPC	800753694750

### Agency

CSA	LR19980
UL	E29179

## Physical

Circuits (maximum)	16
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.829/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Plug Housings	<a href="#"><u>43020</u></a>
Micro-Fit 3.0 Dual Row Headers	<a href="#"><u>43045</u></a>
Micro-Fit 3.0 Dual Row Test Plugs	<a href="#"><u>44242</u></a>

### Use with Part(s)

Description	Part Number
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Tin (Sn) Plating, 150.00mm Length, 20 AWG, Black	<a href="#"><u>797580002</u></a>
Pre-Crimped Lead Micro-Fit 3.0	<a href="#"><u>797580004</u></a>

Female-to-Micro-Fit 3.0 Female, Gold (Au) Plating, 150.00mm Length, 20 AWG, Black	
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Tin (Sn) Plating, 300.00mm Length, 20 AWG, Black	<u>797580010</u>
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Gold (Au) Plating, 300.00mm Length, 20 AWG, Black	<u>797580012</u>
Micro-Fit 3.0 Female Crimp Terminals	<u>43030</u>
Micro-Fit 3.0 Female Crimp Terminals with Lubricant	<u>45773</u>
Micro-Fit Reduced Mating Force Female Crimp Terminals	<u>46235</u>
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female	<u>214760</u>
Pre-Crimped Lead Micro-Fit 3.0 Female-to-Pigtail	<u>214761</u>

---

This document was generated on Apr 24, 2026