REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL DRAWING	OCT18/19	A.G.
B	PRODUCT DRAWING (EAR 15387)	DEC22/23	K.L.


ORDERING CODE: MRU - BF91 - 5000


- SERIES
- USB TYPE
  B=24mm SIZE USB 3.0 TYPE A
- CONNECTOR TYPE
  F=RECEPTACLE
- MOUNTING FEATURE
  9=METAL BAYONET LOCK, WITH PANEL MOUNT (4 SCREWS)
- PLATING
  1=GOLD PLATED ON MATING AREA
- TERMINATION TYPE
  5=RECEPTACLE TO RECEPTACLE ADAPTER
- COVER OPTIONS
  0=WITHOUT DUST COVER
- CABLE LENGTH
  00= NO CABLE


AMPHENOL CANADA CORP RoHS COMPLIANT 2011/65/EU RECAST


NOTES:

1. ALL MATERIALS TO BE RoHS COMPLIANT PER EU DIRECTIVE 2011/65/EU AND AMENDMENTS.
   - FRONT HOUSING: ZINC ALLOY PLATED WITH CHROME
   - INSERT: THERMOPLASTIC PBT, UL FLAMMABILITY RATING 94V-0, BLACK
   - USB CONTACT: COPPER ALLOY PLATED WITH GOLD OVER NICKEL
   - USB SHIELD: COPPER ALLOY PLATED WITH NICKEL
   - USB HOUSING: THERMOPLASTIC LCP, UL FLAMMABILITY RATING 94V-0, BLUE
   - GASKET: SILICONE RUBBER
   - PCB: FR-4 FIBERGLASS, LEAD FREE, UL94V-0 FLAMMABILITY RATING
   - SCREW & HEX NUT: STAINLESS STEEL
2. ELECTRICAL CHARACTERISTICS:
   CURRENT RATING: 0.9A MAX. FOR POSITIONS 1 TO 4, 0.25A MAX. FOR REMAINING POSITIONS
   CONTACT RESISTANCE: 30mΩ MAX. FOR POSITIONS 1 TO 4, 50mΩ MAX. FOR REMAINING POSITIONS
3. RECOMMENDED PANEL THICKNESS: 2.5 (.098) TO 4.0 (.157)
4. ENVIRONMENTAL PROTECTION: IP67 PER IEC 60529 IN MATED CONDITION
5. SCREWS & HEX NUTS PREPARED IN SEPARATE PACKAGE.
6. METAL BAYONET LOCK RECEPTACLE MATES WITH AMPHENOL MRU SERIES PLUGS MRU-BMC1-XXXX.












FRONT RECEPTACLE TO REAR RECEPTACLE CONNECTION CHART

FRONT RECEPTACLE POSITION #	REAR RECEPTACLE POSITION #
1	1
2	2
3	3
4	4
5	8
6	9
7	7
8	5
9	6
SHELL	SHELL



RECOMMENDED PANEL HOLE





THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE	DRAWN F.WANG	OCT18/19
PRIMARY UNITS MILLIMETERS	CHECKED	
SECONDARY INCHES	M.E. APP'D	
REFERENCE IN PARENTHESES	Q.A. APP'D	
GENERAL TOLERANCES	DWG APPR. A.GREEN	OCT18/19
1 DECIMAL PLACE	ENG. REL. NO.	
2 DECIMAL PLACES ±0.25	REF.	
3 DECIMAL PLACES	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING
ANGULAR DEGREES		

Amphenol Canada Corp.
Commercial Products

MRU SERIES RUGGED CONNECTOR, USB 3.0 TYPE A PANEL MOUNT RECEPTACLE, METAL BAYONET LOCK, RECEPTACLE TO RECEPTACLE, IP67 RATING, RoHS COMPLIANT

DWG. NO.	REV
P-MRU-BF91-5000	B

CODE ID NO. 03554 | DWG SIZE: X | SCALE: 1:1 | SHEET 1 OF 1

Downloaded from Arrow.com.