

POWER DISCRETES

Description

Quick reference data

$V_R = 200 - 1000 \text{ V}$
 $I_o = 1.0 \text{ A}$
 $t_{rr} = 150 \text{ to } 500 \text{ ns}$
 $V_F = 1.2 \text{ V}$

Features

- ◆ Low reverse leakage current
- ◆ Hermetically sealed in Metoxilite fused metal oxide
- ◆ Low forward voltage drop

These products are qualified to MIL-PRF-19500/359

Electrical Specifications

Electrical specifications @ $T_A = 25^\circ\text{C}$ unless otherwise specified.

Types	V_{RWM}	$I_F \text{ (AV)}$ @ 55°C		I_{FSM}	I_{FRM} @ $t_p=8.3\text{ms}$	T_{RR}	$V_F @ I_F$		$I_R @ V_{RWM}$		$C_J @ 5\text{V}$ 1MHz	T_{STG}	$R\theta_{jL}$	
		-pcb mid	L = 3/8"						25°C	100°C			3/8"	0"
	V(pk)	A	A	A	A	ns	V	A	μA	μA	pF	°C	C/W°C	C/W°C
1N4942	200	1.0	2.0	25	6.0	150	1.2	1.0	0.5	25	27	-65 to +175	3	7
1N4944	400	1.0	2.0	25	6.0	150	1.2	1.0	0.5	25	27	-65 to +175	3	7
1N4946	600	1.0	2.0	25	6.0	250	1.2	1.0	0.5	25	27	-65 to +175	3	7
1N4947	800	1.0	2.0	25	6.0	250	1.2	1.0	0.5	25	18	-65 to +175	3	7
1N4948	1000	1.0	2.0	25	6.0	500	1.2	1.0	0.5	25	18	-65 to +175	3	7

POWER DISCRETES


Ordering Information

Part Number	Description
1N4942 1N4944 1N4946 1N4947 1N4948	Axial leaded hermetically sealed ⁽¹⁾

Note:

(1) Available in bulk or tape and reel packaging. Please consult factory for quantities.

Outline Drawing



G2

DIM ^N	DIMENSIONS				
	MM		INCHES		NOTE
	MIN	MAX	MIN	MAX	
A	1.6	2.8	.065	.110	—
B	25.4	33.0	1.00	1.30	—
C	3.5	4.2	.140	.165	—
D	—	.80	—	.030	1
E	.66	.84	.026	.033	—

NOTE:

1. LEAD DIAMETER UNCONTROLLED
OVER THIS REGION.