


Data Sheet

Type Number 4276
Designation IEC LR 44
System Manganese Dioxide /
Zinc / KOH - Electrolyte



Nominal Voltage 1,5 V
Typical Capacity C 125 mAh
Load 5.6 kOhm, at 20°C down to 1.2 V

Weight (approx.) 1,8 g
Volume 0,51 ccm
Coding..... Date of Manufacturing
Month/Year

Temperature Ranges	min	max.
Storage	-10°C	65°C
Discharge	-10°C	65°C

Dimensions	min	max.
Diameter (Ø).....	11,25	11,6
Height (A/B).....	5,0	5,4

Segment Electronic

Main Applications Watch
Photo
Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	1.2 V
Continuous	5600 Ω	Time:	482 h
24h/d, 7d/w		Capacity [mAh]:	125
Current [μA]:	270	Energy [mWh]:	168