

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0705530004

Status:


Active

Overview:

SL Modular Connectors

Description:

2.54mm Pitch SL Header, Low Profile, Single Row, Right Angle, 3.05mm Pocket, Shrouded, 5 Circuits, 0.38µm Gold (Au) Selective Plating, Tin (Sn) PC Tail Plating



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

Product Specification PS-70400-001 (PDF)

Product Specification PS-70541-001 (PDF)

Packaging Specification PK-70873-0015-001 (PDF)

Test Summary TS-70541-100-001 (PDF)

RoHS Certificate of Compliance (PDF)

| Agency Certification |  |                             |
|----------------------|--|-----------------------------|
| CSA                  |  | LR19980                     |
| UL                   |  | E29179                      |
| General              |  |                             |
| Product Family       |  | PCB Headers                 |
| Series               |  | 70553                       |
| Application          |  | Signal, Wire-to-Board       |
| Component Type       |  | PCB Header                  |
| Overview             |  | SL Modular Connectors       |
| Product Name         |  | SL                          |
| Taxonomy             |  | PCB Headers and Receptacles |
| UPC                  |  | 800753597396                |

| Physical                       |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | No                             |
| Circuits (Loaded)              | 5                              |
| Circuits (maximum)             | 5                              |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 50                             |
| Flammability                   | 94V-0                          |
| Glow-Wire Capable              | No                             |
| Guide to Mating Part           | Yes                            |
| Lock to Mating Part            | Yes                            |
| Material - Metal               | Brass, Phosphor Bronze         |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 1.112/g                        |
| Number of Rows                 | 1                              |
| Orientation                    | Right Angle                    |
| PC Tail Length                 | 3.30mm                         |
| PCB Locator                    | No                             |
| PCB Retention                  | None                           |
| PCB Thickness - Recommended    | 1.60mm                         |
| Packaging Type                 | Tube                           |
| Pitch - Mating Interface       | 2.54mm                         |
| Plating min - Mating           | 0.381µm                        |
| Plating min - Termination      | 1.905µm                        |
| Polarized to Mating Part       | Yes                            |
| Shrouded                       | Fully                          |
| Stackable                      | No                             |
| Temperature Range - Operating  | -40° to +105°C                 |
| Termination Interface: Style   | Through Hole                   |

| EU ELV                                                        |               |
|---------------------------------------------------------------|---------------|
| Not Relevant                                                  |               |
| EU RoHS                                                       |               |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Contained Per - D(2022)4187-DC (10 June 2022)             |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Low-Halogen                                               |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

70553 Series

Mates With

SL Crimp Housing [70066](#) Option N, [70066](#) Option G, [70430](#) Option G, [70400](#) Option G

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum             | 250V |

**Solder Process Data**

|                                                |      |
|------------------------------------------------|------|
| Duration at Max. Process Temperature (seconds) | 003  |
| Lead-freeProcess Capability                    | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 260  |

**Material Info**

|                    |              |
|--------------------|--------------|
| Engineering Number | A-70553-0004 |
|--------------------|--------------|

**Reference - Drawing Numbers**

|                         |                            |
|-------------------------|----------------------------|
| Packaging Specification | PK-70873-0015-001          |
| Product Specification   | PS-70400-001, PS-70541-001 |
| Sales Drawing           | SDA-70553-XXXX-001         |
| Test Summary            | TS-70541-100-001           |

This document was generated on 01/04/2023

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**