

	1	2	3	4	5	6	7	8																																																																																																																																								
A	har-flexicon terminal block vertical, push-in RoHS compliant				Cable connection <table><tr><td>Type</td><td>har-flexicon 5.0TWPV</td><td>har-flexicon 5.0 TTPV</td></tr><tr><td>Part numbers</td><td>1403xx16101xxx</td><td>1402xx16101xxx</td></tr><tr><td>Conductor size AWG max</td><td colspan="2">12 AWG</td></tr><tr><td>Conductor size AWG min</td><td colspan="2">30 AWG</td></tr><tr><td>Conductor size solid max</td><td colspan="2">2,5 mm²</td></tr><tr><td>Conductor size solid min</td><td colspan="2">0,2 mm²</td></tr><tr><td>Conductor size stranded max</td><td colspan="2">2,5 mm²</td></tr><tr><td>Conductor size stranded min</td><td colspan="2">0,2 mm²</td></tr><tr><td>Conductor size stranded for end sleeve</td><td colspan="2">n.a.</td></tr><tr><td>Stripping length max</td><td colspan="2">10 mm</td></tr><tr><td>Stripping length min</td><td colspan="2">10 mm</td></tr></table> Packging unit <table><tr><td colspan="6">type har-flexicon 5.00 TWPV</td></tr><tr><td>Type of packaging</td><td>No. of poles (xx)</td><td>Quantity</td><td>MOQ</td><td>Index (xxx)</td><td>Remark</td></tr><tr><td>box</td><td>2</td><td>300</td><td>1</td><td>000</td><td></td></tr><tr><td>box</td><td>3</td><td>200</td><td>1</td><td>000</td><td></td></tr><tr><td>box</td><td>4 - 5</td><td>150</td><td>1</td><td>000</td><td></td></tr><tr><td>box</td><td>6 - 12</td><td>100</td><td>1</td><td>000</td><td></td></tr><tr><td>box</td><td>13 - 18</td><td>50</td><td>1</td><td>000</td><td></td></tr></table><table><tr><td colspan="6">type har-flexicon 5.00 TTPV</td></tr><tr><td>Type of packaging</td><td>No. of poles (xx)</td><td>Quantity</td><td>MOQ</td><td>Index (xxx)</td><td>Remark</td></tr><tr><td>tropical bag</td><td>2 - 3</td><td>100</td><td>100</td><td>000</td><td></td></tr><tr><td>tropical bag</td><td>4</td><td>75</td><td>75</td><td>000</td><td></td></tr><tr><td>box</td><td>2 - 4</td><td>1</td><td>1</td><td>333</td><td>sample</td></tr></table> 1403xx16101xxx				Type	har-flexicon 5.0TWPV	har-flexicon 5.0 TTPV	Part numbers	1403xx16101xxx	1402xx16101xxx	Conductor size AWG max	12 AWG		Conductor size AWG min	30 AWG		Conductor size solid max	2,5 mm ²		Conductor size solid min	0,2 mm ²		Conductor size stranded max	2,5 mm ²		Conductor size stranded min	0,2 mm ²		Conductor size stranded for end sleeve	n.a.		Stripping length max	10 mm		Stripping length min	10 mm		type har-flexicon 5.00 TWPV						Type of packaging	No. of poles (xx)	Quantity	MOQ	Index (xxx)	Remark	box	2	300	1	000		box	3	200	1	000		box	4 - 5	150	1	000		box	6 - 12	100	1	000		box	13 - 18	50	1	000		type har-flexicon 5.00 TTPV						Type of packaging	No. of poles (xx)	Quantity	MOQ	Index (xxx)	Remark	tropical bag	2 - 3	100	100	000		tropical bag	4	75	75	000		box	2 - 4	1	1	333	sample																															
Type	har-flexicon 5.0TWPV	har-flexicon 5.0 TTPV																																																																																																																																														
Part numbers	1403xx16101xxx	1402xx16101xxx																																																																																																																																														
Conductor size AWG max	12 AWG																																																																																																																																															
Conductor size AWG min	30 AWG																																																																																																																																															
Conductor size solid max	2,5 mm ²																																																																																																																																															
Conductor size solid min	0,2 mm ²																																																																																																																																															
Conductor size stranded max	2,5 mm ²																																																																																																																																															
Conductor size stranded min	0,2 mm ²																																																																																																																																															
Conductor size stranded for end sleeve	n.a.																																																																																																																																															
Stripping length max	10 mm																																																																																																																																															
Stripping length min	10 mm																																																																																																																																															
type har-flexicon 5.00 TWPV																																																																																																																																																
Type of packaging	No. of poles (xx)	Quantity	MOQ	Index (xxx)	Remark																																																																																																																																											
box	2	300	1	000																																																																																																																																												
box	3	200	1	000																																																																																																																																												
box	4 - 5	150	1	000																																																																																																																																												
box	6 - 12	100	1	000																																																																																																																																												
box	13 - 18	50	1	000																																																																																																																																												
type har-flexicon 5.00 TTPV																																																																																																																																																
Type of packaging	No. of poles (xx)	Quantity	MOQ	Index (xxx)	Remark																																																																																																																																											
tropical bag	2 - 3	100	100	000																																																																																																																																												
tropical bag	4	75	75	000																																																																																																																																												
box	2 - 4	1	1	333	sample																																																																																																																																											
B	General information <table><tr><td colspan="4">PCB Terminal Block</td></tr><tr><td>Type</td><td>har-flexicon 5.0 TWPV</td><td>har-flexicon 5.0 TTPV</td><td></td></tr><tr><td>Part numbers</td><td>1403xx16101xxx</td><td>1402xx16101xxx</td><td></td></tr><tr><td>Contact pitch</td><td>5 mm</td><td></td><td></td></tr><tr><td>No. of contacts</td><td>2 - 18 poles</td><td>2 - 4 poles</td><td></td></tr><tr><td>Rated surge voltage (II/2)</td><td>4 kV</td><td></td><td>(overvoltage cat. II / pollution degree 2)</td></tr><tr><td>Rated surge voltage (III/2)</td><td>4 kV</td><td></td><td>(overvoltage cat. III / pollution degree 2)</td></tr><tr><td>Rated surge voltage (III/3)</td><td>4 kV</td><td></td><td>(overvoltage cat. III / pollution degree 3)</td></tr><tr><td>Rated Voltage</td><td>300 V</td><td></td><td></td></tr><tr><td>Rated voltage (II/2)</td><td>600 V</td><td></td><td>(overvoltage cat. II / pollution degree 2)</td></tr><tr><td>Rated voltage (III/2)</td><td>300 V</td><td></td><td>(overvoltage cat. III / pollution degree 2)</td></tr><tr><td>Rated voltage (III/3):</td><td>300 V</td><td></td><td>(overvoltage cat. III / pollution degree 3)</td></tr><tr><td>Working current</td><td>12 A</td><td></td><td></td></tr><tr><td>Usegroup B, rated voltage / current</td><td>300 V / 12 A</td><td>300 V / 12 A</td><td></td></tr><tr><td>Usegroup C, rated voltage / current</td><td>- / -</td><td>- / -</td><td></td></tr><tr><td>Usegroup D, rated voltage / current</td><td>300 V / 12 A</td><td>300 V / 12 A</td><td></td></tr><tr><td>Contact resistance</td><td>max. 15 mOhm</td><td></td><td></td></tr><tr><td>Insulation resistance</td><td>min. 10⁹ Ohm (500 V DC)</td><td></td><td></td></tr><tr><td>Temperature range</td><td>-40°C ... +110°C</td><td></td><td></td></tr><tr><td>Termination technology</td><td>wave solder</td><td>THR / SMC reflow</td><td></td></tr><tr><td>Insertion force</td><td>n.a</td><td></td><td></td></tr><tr><td>Withdrawal force</td><td>n.a</td><td></td><td></td></tr><tr><td>Hot plugging</td><td>No</td><td></td><td></td></tr><tr><td>Mechanical Shock IEC 61373 (05/10)</td><td>5g/30ms, each 3 shocks, 3 axis/two directions. No contact disturbance > 1µs</td><td></td><td></td></tr><tr><td>Random Vibration IEC 61373 (05/10)</td><td>class1 cat B, ASD level 0,964(m/s²)²/Hz, RMS value 5,72m/s²; 3x5h. No contact disturbance > 1µs</td><td></td><td></td></tr><tr><td>RoHS - compliant</td><td>Yes</td><td></td><td></td></tr><tr><td>UL file</td><td>E314677</td><td></td><td></td></tr></table> Isulator material <table><tr><td></td><td>har-flexicon 5.0 TWPV</td><td>har-flexicon 5.0 TTPV</td></tr><tr><td>Material</td><td>PA</td><td>PA / PPA</td></tr><tr><td>Color</td><td>green</td><td>black / orange</td></tr><tr><td>UL classification</td><td>UL 94-V0</td><td></td></tr><tr><td>Material group acc. to IEC 60664-1</td><td>I (CTI > 600)</td><td></td></tr></table> Contact material <table><tr><td></td><td>termination zone</td><td colspan="2">contact zone</td></tr><tr><td></td><td></td><td>har-flexicon 5.0 TWPV</td><td>har-flexicon 5.0 TTPV</td></tr><tr><td>Contact material</td><td>Copper alloy</td><td>Copper alloy</td><td>1.4310 / AISI 301</td></tr><tr><td>Plating</td><td>Sn</td><td>Ni</td><td>-</td></tr></table> Derating The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals. The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature. Control and test procedures according to DIN IEC 60512-5				PCB Terminal Block				Type	har-flexicon 5.0 TWPV	har-flexicon 5.0 TTPV		Part numbers	1403xx16101xxx	1402xx16101xxx		Contact pitch	5 mm			No. of contacts	2 - 18 poles	2 - 4 poles		Rated surge voltage (II/2)	4 kV		(overvoltage cat. II / pollution degree 2)	Rated surge voltage (III/2)	4 kV		(overvoltage cat. III / pollution degree 2)	Rated surge voltage (III/3)	4 kV		(overvoltage cat. III / pollution degree 3)	Rated Voltage	300 V			Rated voltage (II/2)	600 V		(overvoltage cat. II / pollution degree 2)	Rated voltage (III/2)	300 V		(overvoltage cat. III / pollution degree 2)	Rated voltage (III/3):	300 V		(overvoltage cat. III / pollution degree 3)	Working current	12 A			Usegroup B, rated voltage / current	300 V / 12 A	300 V / 12 A		Usegroup C, rated voltage / current	- / -	- / -		Usegroup D, rated voltage / current	300 V / 12 A	300 V / 12 A		Contact resistance	max. 15 mOhm			Insulation resistance	min. 10 ⁹ Ohm (500 V DC)			Temperature range	-40°C ... +110°C			Termination technology	wave solder	THR / SMC reflow		Insertion force	n.a			Withdrawal force	n.a			Hot plugging	No			Mechanical Shock IEC 61373 (05/10)	5g/30ms, each 3 shocks, 3 axis/two directions. No contact disturbance > 1µs			Random Vibration IEC 61373 (05/10)	class1 cat B, ASD level 0,964(m/s ²) ² /Hz, RMS value 5,72m/s ² ; 3x5h. No contact disturbance > 1µs			RoHS - compliant	Yes			UL file	E314677				har-flexicon 5.0 TWPV	har-flexicon 5.0 TTPV	Material	PA	PA / PPA	Color	green	black / orange	UL classification	UL 94-V0		Material group acc. to IEC 60664-1	I (CTI > 600)			termination zone	contact zone				har-flexicon 5.0 TWPV	har-flexicon 5.0 TTPV	Contact material	Copper alloy	Copper alloy	1.4310 / AISI 301	Plating	Sn	Ni	-	
PCB Terminal Block																																																																																																																																																
Type	har-flexicon 5.0 TWPV	har-flexicon 5.0 TTPV																																																																																																																																														
Part numbers	1403xx16101xxx	1402xx16101xxx																																																																																																																																														
Contact pitch	5 mm																																																																																																																																															
No. of contacts	2 - 18 poles	2 - 4 poles																																																																																																																																														
Rated surge voltage (II/2)	4 kV		(overvoltage cat. II / pollution degree 2)																																																																																																																																													
Rated surge voltage (III/2)	4 kV		(overvoltage cat. III / pollution degree 2)																																																																																																																																													
Rated surge voltage (III/3)	4 kV		(overvoltage cat. III / pollution degree 3)																																																																																																																																													
Rated Voltage	300 V																																																																																																																																															
Rated voltage (II/2)	600 V		(overvoltage cat. II / pollution degree 2)																																																																																																																																													
Rated voltage (III/2)	300 V		(overvoltage cat. III / pollution degree 2)																																																																																																																																													
Rated voltage (III/3):	300 V		(overvoltage cat. III / pollution degree 3)																																																																																																																																													
Working current	12 A																																																																																																																																															
Usegroup B, rated voltage / current	300 V / 12 A	300 V / 12 A																																																																																																																																														
Usegroup C, rated voltage / current	- / -	- / -																																																																																																																																														
Usegroup D, rated voltage / current	300 V / 12 A	300 V / 12 A																																																																																																																																														
Contact resistance	max. 15 mOhm																																																																																																																																															
Insulation resistance	min. 10 ⁹ Ohm (500 V DC)																																																																																																																																															
Temperature range	-40°C ... +110°C																																																																																																																																															
Termination technology	wave solder	THR / SMC reflow																																																																																																																																														
Insertion force	n.a																																																																																																																																															
Withdrawal force	n.a																																																																																																																																															
Hot plugging	No																																																																																																																																															
Mechanical Shock IEC 61373 (05/10)	5g/30ms, each 3 shocks, 3 axis/two directions. No contact disturbance > 1µs																																																																																																																																															
Random Vibration IEC 61373 (05/10)	class1 cat B, ASD level 0,964(m/s ²) ² /Hz, RMS value 5,72m/s ² ; 3x5h. No contact disturbance > 1µs																																																																																																																																															
RoHS - compliant	Yes																																																																																																																																															
UL file	E314677																																																																																																																																															
	har-flexicon 5.0 TWPV	har-flexicon 5.0 TTPV																																																																																																																																														
Material	PA	PA / PPA																																																																																																																																														
Color	green	black / orange																																																																																																																																														
UL classification	UL 94-V0																																																																																																																																															
Material group acc. to IEC 60664-1	I (CTI > 600)																																																																																																																																															
	termination zone	contact zone																																																																																																																																														
		har-flexicon 5.0 TWPV	har-flexicon 5.0 TTPV																																																																																																																																													
Contact material	Copper alloy	Copper alloy	1.4310 / AISI 301																																																																																																																																													
Plating	Sn	Ni	-																																																																																																																																													
C									C																																																																																																																																							
D									D																																																																																																																																							
E									E																																																																																																																																							
F					All rights reserved Department EC PD - DE HARTING Electronics GmbH D-32339 Espelkamp All Dimensions in mm Original Size DIN A3 Scale 1:1 Free size tol. Created by TADJE Inspected by ELLERMANN Standardisation KOHLER Title har-flexicon terminal block vertical, push-in Doc-Key / ECM-Nr. 100579708/UGD/000/C 500000107527 Type DS Number 14037401501 Rev. C Page 1/1																																																																																																																																											