

Technical data sheet

Article number:
111-01136

MCT120R



Product Group	Cable ties for food industry, detectable
Product Family	MCT-Series, PA66MP
Material	Polyamide 6.6, metal detectable (PA66MD)
Colour	Blue (BU)
Bundle Ø max.	100.0 mm
Bundle Ø min.	3.0 mm
Flammability	UL 94 HB
Halogen-free	Yes
Length (L)	387.0 mm
Min.Tensile Strength	535 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	pack
Pack Cont.	100 pcs.
Thickness (T)	1.8 mm
Variant	Inside Serrated
Weight/Unit	0.00282 kg
Width (W)	7.6 mm

